

TM-267 Conductive Sealing Gasket



Characteristic

Easy to attach by pushing with the fingers,
needs no adhesive.
Suitable for protecting edge of panels etc.

Application

Measuring instruments /
Medical instruments /
Kitchen equipments /
Control boards, etc.

Specifications

1. Permissible temperature range -28 to 70°C
2. Recommended plate thickness : 80 to 110% of size B


Parts List

No.	Part Name	Material	Finish	Quantity
1	Trim	PVC	Black	1
2	Core	ALP	Heat Treating	1
3	Tube	CR/EPDM	Black	1


※ Valve (No.3) is not used for TM-267-62-1 to -4.

Specification

Model No.	A	B	C	(D)	E	Code No.			
TM-267-62-1	6.2	2.4	9.3			6131			
TM-267-62-2	5.9	2	9.5			6132			
TM-267-62-3	4.6	0.8	9.7			6133			
TM-267-62-4	5.2	0.5				6134			
TM-267-4100-1	10.9	6.4	12.7	(21.35)	ϕ11.1	6135			
TM-267-4100-2	9.9	4.7	13.6	(20)		6136			
TM-267-4100-3	7.6	3.2	14	(18.1)		6137			
TM-267-4100-4	5.9	1.6	14.5	(16.45)		6138			



TM-267-4100-1 to -4



TM-267-62-1 to -3



TM-267-62-4