

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

56134-9000

Status:

Active

Overview:

MicroClasp™ Wire-to-Board System

Description:

2.00mm Pitch Crimp Terminal 56134, Female, 22-28 AWG, Reel, Copper Alloy, for 51242/51353/51382/500915 Housings

Documents:

- 3D Model

Drawing (PDF)

Product Specification PS-500637-001 (PDF)

Product Specification PS-500730-001 (PDF)

Product Specification PS-51242-002 (PDF)
- Product Specification PS-51353-003 (PDF)

Product Specification PS-51382-004 (PDF)

Packaging Specification SPK-56134-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	56134
Application	Signal
Crimp Quality Equipment	Yes
Overview	MicroClasp™ Wire-to-Board System
Product Name	MicroClasp™
UPC	756054317761

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	36.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.70mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	3A
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-56134-001
Product Specification	PS-500637-001, PS-500730-001, PS-51242-002, PS-51353-003, PS-51382-004, RPS-500637-001, RPS-500730-001, RPS-501844-001, RPS-51216-009, RPS-51216-012, RPS-51242-004, RPS-51242-005, RPS-51242-006, RPS-51242-007, RPS-51353-005, RPS-51353-008, RPS-51353-009, RPS-51353-010, RPS-51353-013, RPS-51353-014, RPS-51353-016, RPS-51353-017, RPS-51353-018, RPS-51353-019, RPS-51353-020, RPS-51353-022, RPS-51353-024, RPS-51353-025, RPS-51353-026, RPS-51353-027, RPS-51353-031, RPS-51353-033, RPS-51353-034, RPS-51382-006, RPS-51382-007, RPS-51382-008,




image - Reference only

Series

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

56134Series

Use With

500915 Dual Row Crimp Housing, 51242 Dual Row Crimp Housing, 51353 Dual Row Crimp Housing, 51382 Single Row Crimp Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0638116300
Insertion Tool	0011020022
FineAdjust™	0639019600
Applicator for 2.00mm Pitch Female Crimp Terminal	

Sales Drawing

RPS-51382-009, RPS-51382-010, RPS-51382-011,
RPS-51382-012, RPS-51382-013, RPS-51382-014,
RPS-51382-015, RPS-51382-018
SD-56134-005

T2 Terminator for 2.00mm Pitch Female Crimp Terminal	<u>0639119600</u>
Extraction Tool	<u>0638132700</u>
Japan	
Description	Product #
Applicator for M211A Bench Press, 18-22 AWG Wire	<u>0574043000</u>
Side-Feed Applicator for Full-Auto Machine	<u>0574043200</u>

This document was generated on 07/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[56134-9000](#) [56134-9000 \(Mouser Reel\)](#) [56134-9000 \(Cut Strip\)](#)