








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H5	REVISED	ECR-17-002468	06MAR2017	TS KB



- ④ Z面より2mmの範囲で測定。
2. 適用プリント基板厚：1.6mm
3. 嵌合相手ハウジング型番：174046
4. 推奨取付けねじ：JIS B1115, B1122 タッピンねじ, なべ2種
呼び径3, 長さ7mm以上 (締付けトルク：0.4N-m以下)
⑤ 回路番号：FIG.1 参照
6. 製品規格番号：108-5244, 取扱説明書：411-5883
- ④ TO BE MEASURED WITHIN 2mm FROM Z
2. APPLICABLE P.C.BOARD THICKNESS: 1.6mm
3. THE MATING PLUG HOUSING PART NUMBER: 174046
4. RECOMMENDED MOUNTING SCREW: 3mm DIA, 7mm LENGTH (MIN.)
PAN HEAD, CLASS 2 TAPPING SCREW SPRICIFIED IN JIS B1115,
B1122 (TIGHTENING TORQUE: 0.4N-m MAX.)
⑤ CIRCUIT NUMBER: SEE FIG.1
6. PRODUCT SPECIFICATION: 108-5244
INSTRUCTION SHEET: 411-5883



⑤ FIG.1



TOLERANCE UNLESS OTHERWISE SPECIFIED:	
0<×≤ 10	: ±0.2
10<×≤ 30	: ±0.25
30<×≤ 100	: ±0.3
ANGLE	: ±3°
角度	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
	FINISH
MATERIAL	SEE TABLE
HOUSING: PBT	
CONTACT: BRASS	

SELECTIVE TIN (MATTE)		SELECTIVE GOLD x 16	1~16	BLACK 黒色	1-5174053-2
TIN-LEAD		SELECTIVE GOLD x 2	5,6	BLACK 黒色	3-174053-2
PRE-TIN x 14					
SEE DWG 2-174053-2					2-174053-2
TIN-LEAD		SELECTIVE GOLD x 16	1~16	BLACK 黒色	1-174053-2
PRE-TIN x 16			-	BLUE 青色	174053-5
PRE-TIN x 16			-	GREEN 緑色	174053-4
PRE-TIN x 16			-	BLACK 黒色	174053-2
SOLDERING SIDE 半田付け部		CONTACT SIDE 接触部創		△ GOLD PLATED CIRCUIT NO. 金めっき回路番号	COLOR 色
CONTACT FINISH コンタクト仕上					
DWN T.SHINOHARA		06JAN09		TE Connectivity	
CHK K.BETSUI		06JAN09			
APVD K.BETSUI		06JAN09			
PRODUCT SPEC		NAME			
SEE NOTE 6		040 SERIES MULTI-LOCK I/O CONNECTOR 16POSITION CAP HOUSING ASSEMBLY			
APPLICATION SPEC					
—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
WEIGHT 8.4 g		A2	00779	C-174053	—
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV H5