

# Miniature Steel Alligator Clip, 5 Amp

## Features

- Nickel Plated
- Crimp or Solder Connection
- Overall Length: 1.100" (27.9mm)
- Jaw Opening: .190" (4.8mm)

| NTE Type No. | Description                    |
|--------------|--------------------------------|
| 72-123       | Miniature Steel Alligator Clip |

See page 24 for recommended insulators.



See page 15 for clip & insulator combinations.

# Miniature Solid Copper Alligator Clip, 5 Amp

## Features

- Crimp or Solder Connection
- Overall Length: 1.100" (27.9mm)
- Jaw Opening: .190" (4.8mm)

| NTE Type No. | Description                           |
|--------------|---------------------------------------|
| 72-125       | Miniature Solid Copper Alligator Clip |

See page 24 for recommended insulators.



See page 15 for clip & insulator combinations.

# Mini Steel Alligator Clip w/Barrel, 5 Amp

## Features

- Nickel Plated
- Crimp or Solder Connection Barrel Tail
- Overall Length: 1.250" (31.7mm)
- Jaw Opening: .190" (4.8mm)

| NTE Type No. | Description                                |
|--------------|--------------------------------------------|
| 72-124       | Miniature Steel Alligator Clip with Barrel |

See page 24 for recommended insulators.



See page 15 for clip & insulator combinations.

# Mini Steel Alligator Clip w/Threaded Barrel, 5 Amp

## Features

- Nickel Plated
- 6-32 UNC Threaded Barrel Connection
- Overall Length: 1.500" (38.1mm)
- Jaw Opening: .190" (4.8mm)

| NTE Type No. | Description                                         |
|--------------|-----------------------------------------------------|
| 72-126       | Miniature Steel Alligator Clip with Threaded Barrel |

See page 24 for recommended insulators.



# Steel Alligator Clip, 5 Amp

## Features

- Nickel Plated Clip
- Crimp/Solder Connection
- Overall Length: 1.690" (42.9mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description          |
|--------------|----------------------|
| 72-159       | Steel Alligator Clip |

See page 26 for recommended insulators.



See page 16 for clip & insulator combinations.

# Steel Alligator Clip w/Screw, 5 Amp

## Features

- Nickel Plated Clip
- 6-40 Screw or Crimp Connection
- Overall Length: 1.690" (42.86mm)
- Jaw Opening: .310" (7.9mm)

| NTE Type No. | Description                     |
|--------------|---------------------------------|
| 72-186       | Steel Alligator Clip with Screw |



# Toothless Steel Alligator Clip, 5 Amp

## Features

- Smooth Micro Tipped Jaws
- Crimp or Solder Connection
- Overall Length: 1.100" (27.9mm)
- Jaw Opening: .220" (5.58mm)

| NTE Type No. | Description                    |
|--------------|--------------------------------|
| 72-129       | Toothless Steel Alligator Clip |

See page 24 for recommended insulators.



See page 15 for clip & insulator combinations.

# Toothless Solid Copper Alligator Clip, 5 Amp

## Features

- Smooth Micro Tipped Jaws
- Crimp or Solder Connection
- Overall Length: 1.100" (27.9mm)
- Jaw Opening: .220" (5.58mm)

| NTE Type No. | Description                           |
|--------------|---------------------------------------|
| 72-130       | Toothless Solid Copper Alligator Clip |

See page 24 for recommended insulators.



See page 16 for clip & insulator combinations.

# Steel Alligator Clip w/Barrel, 10 Amp

## Features

- Nickel Plated
- Crimp/Solder or Banana Plug Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                      |
|--------------|----------------------------------|
| 72-148       | Steel Alligator Clip with Barrel |

See page 25 for recommended insulators.



See page 16 for clip & insulator combinations.

# Solid Copper Alligator Clip w/Barrel, 10 Amp

## Features

- Crimp/Solder or Banana Plug Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                             |
|--------------|-----------------------------------------|
| 72-149       | Solid Copper Alligator Clip with Barrel |

See page 25 for recommended insulators.



See page 17 for clip & insulator combinations.

# Solid Copper Alligator Clip w/Barrel & Screw, 10 Amp

## Features

- Screw Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                                     |
|--------------|-------------------------------------------------|
| 72-151       | Solid Copper Alligator Clip with Barrel & Screw |

See page 25 for recommended insulators.



See page 17 for clip & insulator combinations.

# Steel Alligator Clip w/Barrel & Screw, 10 Amp

## Features

- Nickel Plated
- Screw Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                              |
|--------------|------------------------------------------|
| 72-153       | Steel Alligator Clip with Barrel & Screw |

See page 25 for recommended insulators.



See page 17 for clip & insulator combinations.

# Steel Alligator Clip w/Threaded Barrel, 10 Amp

## Features

- Nickel Plated
- 8-32 UNC Threaded Barrel Connection
- Overall Length: 2.125" (53.9mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                               |
|--------------|-------------------------------------------|
| 72-154       | Steel Alligator Clip with Threaded Barrel |

See page 25 for recommended insulators.



See page 17 for clip & insulator combinations.

# Steel Alligator Clip w/U-Shaped Tail, 10 Amp

## Features

- Nickel Plated Clip
- Crimp/Solder Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                             |
|--------------|-----------------------------------------|
| 72-155       | Steel Alligator Clip with U-Shaped Tail |

See page 25 for recommended insulators.



See page 18 for clip & insulator combinations.

# Stainless Steel Alligator Clip w/Barrel, 10 Amp

## Features

- Crimp/Solder or Banana Plug Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                                |
|--------------|--------------------------------------------|
| 72-156       | Stainless Steel Alligator Clip with Barrel |

See page 25 for recommended insulators.



See page 18 for clip & insulator combinations.

# Solid Copper Alligator Clip, 10 Amp

## Features

- Crimp/Solder Connection
- Overall Length: 1.690" (42.9mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                 |
|--------------|-----------------------------|
| 72-160       | Solid Copper Alligator Clip |

See page 26 for recommended insulators.



See page 18 for clip & insulator combinations.

# Phone Tip Steel Alligator Clip, 10 Amp

## Features

- Nickel Plated Clip
- Accepts Standard Phone Tip or Test Probe Tip
- Overall Length: 1.970" (50mm)
- Jaw Opening: .310" (7.9mm)

| NTE Type No. | Description                    |
|--------------|--------------------------------|
| 72-181       | Phone Tip Steel Alligator Clip |

See page 25 for recommended insulators.




# Solid Copper Alligator Clip w/Screw, 10 Amp

## Features

- 6-40 Screw or Crimp Connection
- Overall Length: 1.690" (42.86mm)
- Jaw Opening: .310" (7.9mm)

| NTE Type No. | Description                            |
|--------------|----------------------------------------|
| 72-187       | Solid Copper Alligator Clip with Screw |



# Steel Alligator Clip, Fang Tooth w/Barrel

## Features

- Nickel Plated Clip
- Crimp/Solder or Banana Plug Connection
- Grips Both Fine and Thick Conductors
- Overall Length: 1.920" (48.7mm)
- Jaw Opening: .390" (9.9mm)

| NTE Type No. | Description                                  |
|--------------|----------------------------------------------|
| 72-098       | Steel Alligator Clip, Fang Tooth with Barrel |



# Steel Alligator Clip w/Barrel, Screw & Handle, 10 Amp

## Features

- Nickel Plated Clip with Insulated Handle
- Banana Plug or Screw Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                                                        |
|--------------|--------------------------------------------------------------------|
| 72-152-0     | Steel Alligator Clip with Barrel, Screw and Black Insulated Handle |
| 72-152-2     | Steel Alligator Clip with Barrel, Screw and Red Insulated Handle   |
| 72-152-KIT   | 2 Each of 72-152-0 (Black) & 72-152-2 (Red)                        |



# Solid Copper Alligator Clip w/Barrel, Screw & Handle, 10 Amp

## Features

- Solid Copper Clip with Insulated Handle
- Banana Plug or Screw Connection
- Overall Length: 2.344" (59.53mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                                                                |
|--------------|----------------------------------------------------------------------------|
| 72-150-0     | Solid Copper Alligator Clip with Barrel, Screw and Black Insulated Handle  |
| 72-150-2     | Solid Copper Alligator Clip with Barrel, Screw and Red Insulated Handle    |
| 72-150-4     | Solid Copper Alligator Clip with Barrel, Screw and Yellow Insulated Handle |
| 72-150-5     | Solid Copper Alligator Clip with Barrel, Screw and Green Insulated Handle  |
| 72-150-6     | Solid Copper Alligator Clip with Barrel, Screw and Blue Insulated Handle   |
| 72-150-9     | Solid Copper Alligator Clip with Barrel, Screw and White Insulated Handle  |
| 72-150-KIT   | 2 Each of 72-150-0 (Black) & 72-150-2 (Red)                                |



# Steel Alligator Clip, Insulated, 10 Amp

## Features

- Nickel Plated Clip
- Includes Skin Tight Insulation
- Banana Plug or Screw Connection
- Overall Length: 2.125" (53.9mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                                         |
|--------------|-----------------------------------------------------|
| 72-158-0     | Steel Alligator Clip w/Skin Tight Insulation, Black |
| 72-158-2     | Steel Alligator Clip w/Skin Tight Insulation, Red   |
| 72-158-KIT   | 2 Each of 72-158-0 (Black) & 72-158-2 (Red)         |



# Steel Alligator Clip w/Insulated Handle, 10 Amp

## Features

- Nickel Plated Clip
- Tenite Acetate Insulated Handle
- Overall Length: 2.234" (56.75mm)
- Jaw Opening: .310" (7.87mm)

| NTE Type No. | Description                                      |
|--------------|--------------------------------------------------|
| 72-185-0     | Steel Alligator Clip with Black Insulated Handle |
| 72-185-2     | Steel Alligator Clip with Red Insulated Handle   |




# Telecom Clip, Bed of Nails & Single Spike Combo

## Features

- Nickel-Silver Jaw Material
- Ideal for Telecom Applications
- Crimp or Solder Connection
- Overall Length: 2.600" (66.0mm)
- Jaw Opening: 1.000" (25.4mm)

| NTE Type No. | Description                                    |
|--------------|------------------------------------------------|
| 72-096       | Insulator-Piercing Alligator Clip, Glove Style |

See page 27 for recommended insulators.



See page 21 for clip & insulator combinations.


# Telecom Clip, Bed of Nails & Single Spike Combo

## Features

- Nickel-Silver Jaw Material
- Ideal for Telecom Applications
- Crimp or Solder Connection
- Overall Length: 2.600" (66.0mm)
- Jaw Opening: 1.000" (25.4mm)

| NTE Type No. | Description                                                    |
|--------------|----------------------------------------------------------------|
| 72-167       | Insulator-Piercing Alligator Clip, Mitten Style, with Hardware |
| 72-168       | Insulator-Piercing Alligator Clip, Mitten Style                |

See page 26 for recommended insulators.



See page 22 for clip & insulator combinations.