




(2,54 mm) .100"

BBS, BBL, BHS, BBD, BDL SERIES

MACHINED BOARD STACKING STRIPS

Mates with:

SS, SD, HSS, SL, SDL, ESS, ESD

FEATURES

- Low profile design achieves (3,89 mm) .153" board spacings when mated with SL Series.
- Approach the reliability of a permanent connection with the flexibility of a separable connection.

SPECIFICATIONS

For complete specifications see www.samtec.com?BBS, www.samtec.com?BBL, www.samtec.com?BHS, www.samtec.com?BBD or www.samtec.com?BDL

Insulator Material:

Black Glass Filled Polyester (BBS, BBD, BBL)
Black High Temp Nylon (BDL)
Black Liquid Crystal Polymer (BHS)

Temperature Range:
-55°C to +125°C

Terminal Material:

Phosphor Bronze or Brass

Plating:

Au or Sn over 50µ" (1,27 µm) Ni
RoHS Compliant:
Yes

Lead-Free Solderable:

Wave only (BBS, BBD, BBL, BDL)
Wave, or reflow with all Au (BHS)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note: Some lengths, styles and options are non-standard, non-returnable.

