




Dimensions: in.
(except where noted)



■ SPECIFICATIONS:

- Primary voltage: 120VAC 60Hz
- Exciting current, open circuit: 50mA(no load)
70mA max.(loaded)
- Primary DC resistance: $270\Omega \pm 15\%$
- Secondary, no load voltage: 32.8VDC
- Loaded voltage: 24VDC 100mA
- Secondary DC resistance: $11.5\Omega \pm 10\%$
- Insulation resistance: $100M\Omega @ 500VDC$
- Dielectric strength: 500VAC for 1 minute
- Core: silicon steel, EI-35, H50N50
- Cord length: 6ft.

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[412-124013](#)