



| APPLICATION SPECIFIC |       |        |        |      |       |
|----------------------|-------|--------|--------|------|-------|
| PIN                  | STYLE | MATING | SOLDER | "C"  | "J"   |
| 03                   |       | 5.84   | 2.41   | 1.52 | 12.44 |
| 04                   |       | 5.84   | 3.05   | 1.52 | 12.44 |
| 06                   |       | 10.72  | 13.39  | 1.52 | 17.32 |
| 07                   |       | 12.32  | 13.39  | 1.52 | 18.92 |
| 08                   |       | 3.05   | 3.05   | 1.52 | 9.65  |
| 09                   |       | 6.04   | 1.6    | 1.52 | 12.64 |
| 10                   |       | 10.89  | 3.05   | 1.52 | 17.49 |
| 14                   |       | 5.82   | 7.8    | 1.4  | 12.3  |
| 15                   |       | 3.2    | 10     | 1.52 | 9.8   |
| 18                   |       | 3.5    | 6.4    | 1.4  | 10    |
| 20                   |       | 13     | 3.23   | 1.52 | 19.6  |
| 22                   |       | 7.48   | 1.6    | 1.52 | 14.08 |

|             |                |     |          |                                       |             |                  |  |            |                |  |                  |      |
|-------------|----------------|-----|----------|---------------------------------------|-------------|------------------|--|------------|----------------|--|------------------|------|
| mat'l. code |                |     |          | surface                               |             | tolerance        |  | projection | product family |  |                  |      |
|             |                |     |          | ISO 1302 ✓                            |             | ISO 406 ISO 1101 |  |            | BSTIK          |  |                  |      |
| ltr         | ecn no         | dr  | date     | tolerances unless otherwise specified |             |                  |  |            | title          |  |                  |      |
| AA          | F00135         | DLE | 00.02.23 | angles                                | linear      |                  |  |            | HEADER,DR,RA,  |  |                  |      |
| AB          | F00145         | LMU | 00.03.07 |                                       |             |                  |  |            | 2.54 mm        |  |                  |      |
| AC          | F00461         | LMU | 00.07.11 |                                       |             |                  |  | scale      |                |  |                  |      |
| AD          | F20116         | DLE | 02.01.17 | dr                                    | G LEOTY     | 95.08.26         |  |            | dwg no         |  | sheet 2 of -     | size |
| AE          | F03-0203       | LMU | 03.04.28 | enr                                   | COMPAGNON J | 95.08.26         |  |            | 76350          |  |                  | A3   |
| AF          | F05-0186       | LMU | 05.06.09 | chr                                   |             |                  |  |            |                |  |                  |      |
| AG          | F06-0207       | LMU | 06.07.27 | appd                                  | JMC         | 95.08.26         |  |            | type           |  | CUSTOMER Drawing |      |
| sheet index | revision sheet |     |          |                                       |             |                  |  |            |                |  |                  |      |