


LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
G	86				K	REV PER 063A-0561-01	090CT02	JR MS



- 1 CIRCULAR MIL RANGE: 750-850 MCM
2 TIN PL 0.00381 [0.000150] MIN THK PER MIL-T-10727

326405			
PART NO			
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [0.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75 FINISH △		DR 9/17/91 DK SCHRUM CHK 9/17/91 AJ KAUFMAN APPD 9/18/91 WJ VOCKROTH APPD 9/18/91 AJ ADELMANN PRODUCT SPEC - APPLICATION SPEC - WEIGHT .593 LB	
		AMP AMP INCORPORATED Harrisburg, Pa. 17105 NAME TERMINAL, AMPPOWER™ WIRE SIZE: 405.0mm ² [800] MCM SIZE C CAGE CODE 00779 DRAWING NO 326405 SCALE 1:1 SHEET 1 OF 1	

METRIC