

On single pole models positions 1 & 3 are support pins

[illegible]

POS.1	POS.2
	
ON	ON
2-3, 5-6	2-1, 5-4
	

- Contact Rating: 0.4VA Max. @ 20V AC or DC Max.
- Contact Resistance: Below 100mΩ typ. initial
- Insulation Resistance: 500MΩ min.
- Dielectric Strength: 500Vrms min.

- RoHS Compliant

- Life: 40,000 make-and-break cycles
- Operating Temperature: -30°C~+85°C

- Only for Wave Soldering, do not use in IR-Reflow Soldering

103-7139-EV

Mountain Switch

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-7139-EV](#)