



CRIMPERS



www.eclipsetools.com

• All dies on pgs3,4, 5 & 6 fit each of these frames

Ergo-Lunar Crimp Frame




Description	Part No.
Ergo-Lunar Crimp Frame w/Screws (No Die)	300-096
Replacement Die Screw	300-056

Lunar Crimp Frame



Description	Part No.
Frame w/Screws (No Die)	300-054
Replacement Die Screw	300-056

CrimPro Crimp Frame



Our Best Frame

Eclipse Tools

Description	Part No.
CrimPro Tool, Frame-Only, No Die Set	902-085

• Ergo-Lunar Crimp Frame



• Lunar Crimp Frame



• CrimPro Crimp Frame



DIE Set	Application	Crimp Size	Description	Part No.
	RG58, 59 and 62 AU, BNC and TNC 3-piece connectors	.256 .213 .068	Lunar frame w/die	300-019
			Ergo-Lunar frame w/die	300-109
			CrimPro frame w/die	902-143
			Die only	300-045
	Cambridge Products' BNC's RG58, RG59, 62AU, CP-88-1, CP-88-2, CP-89-1, CP-89-2 series Cambridge connectors & others	.305 .228 .068	Lunar frame w/die	300-020
			Ergo-Lunar frame w/die	300-110
			CrimPro frame w/die	902-144
			Die only	300-046
	CATV "F" connectors RG-59, RG-6 and RG-6 Quad	.350 .320 .255	Lunar frame w/die	300-007
			Ergo-Lunar frame w/die	300-112
			CrimPro frame w/die	902-139
			Die only	300-041
	AMP BNC /TNC RG58 (round)	.218 .049	Lunar frame w/die	300-025
			Ergo-Lunar frame w/die	300-113
			CrimPro frame w/die	902-149
			Die only	300-051
	AMP BNC /TNC RG59/62AU (round & round, square)	.240 .042	Lunar frame w/die	300-026
			Ergo-Lunar frame w/die	300-114
			CrimPro frame w/die	902-150
			Die only	300-052
	AT&T 735(A), RG58 and RG174 cable groups both 50 and 75 ohm center pins (Thinnet)	.213 .178 .155 .068 .042	Lunar frame w/die	300-021
			Ergo-Lunar frame w/die	300-115
			CrimPro frame w/die	902-145
			Die only	300-047
	RG59 and Belden 8281/1694A cable groups for both 50 & 75 ohm center pins	.324 .255 .068 .042	Lunar frame w/die	300-022
			Ergo-Lunar frame w/die	300-116
			CrimPro frame w/die	902-146
			Die only	300-048
	RG8, RG11, RG213, RG216 BNC, TNC and N Series Connectors LMR400	.429 .100 .080	Lunar frame w/die	300-023
			Ergo-Lunar frame w/die	300-117
			CrimPro frame w/die	902-147
			Die only	300-049
	RG174/179 Belden 1855, HDTV Compatible kings/ADC/Amphenol	.178 .128 .068 .151 .078 .042	Lunar frame w/die	300-024
			Ergo-Lunar frame w/die	300-118
			CrimPro frame w/die	902-148
			Die only	300-050
	BNC, TNC, Mini-UHF, RG58, 141, 142, 303, 400, 59, 62, 210 Belden 8279, 8281, 9231, 9141 RG-6, 212, 222, 304	.321 .255 .213 .098 .068	Lunar frame w/die	300-003
			Ergo-Lunar frame w/die	300-119
			CrimPro frame w/die	902-137
			Die only	300-038

Eclipse Tools

• Ergo-Lunar Crimp Frame



• Lunar Crimp Frame



• CrimPro Crimp Frame



DIE Set	Application	Crimp Size	Description	Part No.
	Cambridge-AIM connectors RG6, RG8, RG59, RG62, 3pc BNC/TNC	.390 .275 .065	Lunar frame w/die	300-066
			Ergo-Lunar frame w/die	300-121
			CrimPro frame w/die	902-153
			Die only	300-059
	Cambridge-AIM connectors-RG58U, RG58AU, RG174, RG139, RG185, RG188, RG316, 3pc BNC/TNC	.235 .128 .065 .042	Lunar frame w/die	300-067
			Ergo-Lunar frame w/die	300-122
			CrimPro frame w/die	902-154
			Die only	300-060
	Cambridge-AIM connectors-RG58U, RG58AU, RG59 Teflon, RG62 Teflon 2 & 3pc BNC/TNC, 1/2" F-Type	.324 .216 .068 .360	Lunar frame w/die	300-068
			Ergo-Lunar frame w/die	300-123
			CrimPro frame w/die	902-155
			Die only	300-061
	Cambridge-AIM connectors-RG6, RG58 2pc BNC/TNC, w/standard Ring by Amphenol, Kings	.320 .210 .185	Lunar frame w/die	300-069
			Ergo-Lunar frame w/die	300-124
			CrimPro frame w/die	902-156
			Die only	300-062
	Twinax	.429 .075 .075	Lunar frame w/die	300-034
			Ergo-Lunar frame w/die	300-125
			CrimPro frame w/die	902-157
			Die only	300-065
	RG58, 174 Fiber Optic SC/ST/FC/LC	.100" .213" .128" .190"	Lunar frame w/die	300-154
			Ergo-Lunar frame w/die	300-155
			CrimPro frame w/die	902-170
			Die only	300-153
	Fiber Optic and Coaxial SMA/SMB/ SFR Connectors SC/ST/FC	.213 .178 .151	Lunar frame w/die	300-106
			Ergo-Lunar frame w/die	300-143
			CrimPro frame w/die	902-167
			Die only	300-102
	Broadcast Applications Belden 1855/1505/1694, Kings/ADC/Trompeter/Amphenol	.042 .068 .178 .278 .255	Lunar frame w/die	300-158
			Ergo-Lunar frame w/die	300-159
			CrimPro frame w/die	902-171
			Die only	300-157
	Amphenol and General RG58, RG59, RG62, BNC/TNC, F-Type	.052 .068 .100 .213 .255	Lunar	902-277
			Ergo-Lunar	902-278
			CrimPro	902-279
			Die only	902-201
	RJ45 modular plugs 8 position (Standard plugs, not AMP)		Lunar frame w/die	300-012
			Ergo-Lunar frame w/die	300-126
			CrimPro frame w/die	902-140
			Die only	300-042

Eclipse Tools

• Ergo-Lunar Crimp Frame



• Lunar Crimp Frame



• CrimPro Crimp Frame



DIE Set	Application	Crimp Size	Description	Part No.
	RJ11 modular plugs 2, 4 and 6 position (WE/Stewart style only)		Lunar frame w/die	300-027
			Ergo-Lunar frame w/die	300-127
			CrimPro frame w/die	902-151
			Die only	300-053
	RJ45 modular plugs 8 position(AMP) keyed and non-keyed		Lunar frame w/die	300-017
			Ergo-Lunar frame w/die	300-128
			CrimPro frame w/die	902-142
			Die only	300-044
	RJ50 modular plugs 10 position Virginia Plastics style		Lunar frame w/die	300-013
			Ergo-Lunar frame w/die	300-129
			CrimPro frame w/die	902-141
			Die only	300-043
	RJ22 2 & 4 Pin Handset Plugs		Lunar frame w/die	300-135
			Ergo-Lunar frame w/die	300-136
			CrimPro frame w/die	902-163
			Die only	300-098
	RJ11 DEC MMJ 6 pos, Offset Plugs		Lunar frame w/die	300-137
			Ergo-Lunar frame w/die	300-138
			CrimPro frame w/die	902-164
			Die only	300-099
	RJ11 AMP Style 2, 4 & 6 pos, Plugs		Lunar frame w/die	300-139
			Ergo-Lunar frame w/die	300-140
			CrimPro frame w/die	902-165
			Die only	300-100
	Open barrel contacts AWG 20-18, 16-14, 12-10 D-sub, Molex, AMP style pin		Lunar frame w/die	300-005
			Ergo-Lunar frame w/die	300-120
			CrimPro frame w/die	902-138
			Die only	300-039
	Combi-Die for RJ45 WE/SS Modular plugs and RG6/6Q(CATV F-Type)	RJ45 plug and hex size.324/.360	Lunar frame w/die	300-161
			Ergo-Lunar frame w/die	300-162
			CrimPro frame w/die	902-172
			Die only	902-054
	Red, Yellow, Blue Insulated terminals AWG 10-12, 14-16, 18-20 Nylon and Vinyl		Lunar frame w/die	300-002
			Ergo-Lunar frame w/ die	300-108
			CrimPro frame w/die	902-152
			Die only	300-058

• Ergo-Lunar Crimp Frame



• Lunar Crimp Frame




• CrimPro Crimp Frame



DIE Set	Application	Crimp Size	Description	Part No.
	Insulated Flag Terminals AWG 22-18, 16-14		Lunar frame w/die	300-072
			Ergo-Lunar frame w/ die	300-130
			CrimPro frame w/die	902-158
			Die only	300-070
	Uninsulated Flag Terminals AWG 22-18, 16-14		Lunar frame w/die	300-073
			Ergo-Lunar frame w/ die	300-131
			CrimPro frame w/die	902-159
			CrimPro frame w/die	300-071
	Uninsulated Terminals AWG 20-18, 16-14, 12-10, 8		Lunar frame w/die	300-132
			Ergo-Lunar frame w/ die	300-133
			CrimPro frame w/die	902-161
			Die only	300-095
	Thin Style Insulated Terminals (red/yellow/blue) AWG 22-10 Nylon and Vinyl		Lunar frame w/die	300-141
			Ergo-Lunar frame w/ die	300-142
			CrimPro frame w/die	902-166
			Die only	300-101
	Miniature Insulated Terminals AWG 26-16 Nylon and Vinyl		Lunar frame w/die	300-146
			Ergo-Lunar frame w/ die	300-147
			CrimPro frame w/die	902-169
			Die only	300-104
	Wire ferrules AWG 22-12 (Insulated and Non-Insulated)		Lunar frame w/die	300-001
			Ergo-Lunar frame w/ die	300-134
			CrimPro frame w/die	902-162
			Die only	300-097
	Wire Ferrules AWG 10-6 (Insulated and Non-Insulated)		Lunar frame w/die	300-144
			Ergo-Lunar frame w/ die	300-145
			CrimPro frame w/die	902-168
			Die only	300-103
	AWG 2-4-6 (Insulated and Non-Insulated)	Wire Ferrules	Lunar frame w/die	300-077
			Ergo-Lunar frame w/die	300-160
			CrimPro frame w/die	902-160
			Die only	300-077D
	Spark Plug Cable-Cut, Strip, Crimp		Ergo-Lunar frame w/die	902-275 
			CrimPro frame w/die	902-276 
			Die only	9PK-3003D26 

Solar Series Crimpers

Description	Part No.
Frame Only	300-087



DIE Set	Application	Crimp Size	Description	Part No.
	D-Subminiature contacts, RS232 pins & sockets AWG 30-18 Open Barrel contacts (Molex/AMP style)		Tool including die	300-009
			Die only	300-086
	Wire Ferrules AWG 22-10		Tool including die	300-010
			Die only	300-105

Modular Plug Crimp Tool



- Strips and cuts 4 pair UTP and up to 8 wire flat satin cable
- Crimp 4 pin ,6 pin and 8 pin plugs.
- Material: ABS + carbon steel

Description	Application	Part No.
Modular Plug Crimp Tool	4P/6P/8P (RJ45, RJ22, RJ11, RJ12)	902-086

Economy Modular Plug Crimper




- Handset plugs
- Cuts, strips and crimps all-in-one
- Crimps stewart style modular plugs
- 4,6 & 8 position plugs


Description	Part No.
Economy Modular Plug Crimper	300-037

Eclipse Tools

Modular Crimp Tool-Standard



- Strips and cuts 4 pair UTP and up to 8 wire flat satin cable
- Crimp 4 pin ,6 pin and 8 pin plugs



Description	Part No.
Modular Plug Crimper RJ11 2, 4 & 6 Position RJ45 8 Position	300-004
Replacement Blade	300-004B

Economy All-In-One Modular Plug Crimper



Item #: 300-018
RJ11 and RJ45



Item #: 300-028
RJ45 and RJ11
DEC/MMJ



Item #: 300-078
RJ11 and RJ22
Handset

- Non-ratcheted design
- Cuts, strips and crimps in one tool

All-in One Modular Plug Crimper



Item #: 300-063
RJ11 and RJ45



Item #: 300-064
AMP style RJ22
Handset /RJ11/RJ11 DEC/
MMJ/RJ45/RJ50



Item #: 300-080
WW/SS style RJ22 Handset
/RJ11/ RJ11 DEC/MMJ/RJ45

- Ratcheted design
- Our best quality modular plug crimpers

Description	Part No.
Standard plugs; 6 position & 8 Position	300-018
DEC/MMJ plugs only;6 Position & 8 Position Keyed	300-028
4 Postion Handset Plugs and 6 Position Plugs	300-078
Replacement Blades for 300-018, 300-028, 300-078	200-053


Eclipse Tools

Description	Part No.
Standard Style Plugs 6 and 8 position	300-063
Replacement Blade for 300-063	900-078
Premium Crimper AMP Style Plugs only; 6, 8 & 10 Position Plugs ,6 Position DEC	300-064
Premium Crimper Standard Style Plugs; 4, 6 & 8 Position Plugs ,6 Position DEC	300-080

Economy All-In-One Modular Plug Crimper



- Cuts/strips/crimps all in one tool
- Our best value for modular plug crimpers



Cutting




Stripping UTP / STP Cable



Stripping



Crimping



Safety latch

Description	Part No.
4 Position handset plugs only , and RJ22 Handset	300-088
6 Position, and RJ11, RJ12	300-089
8 Position, and RJ45	300-090
Replacement Blades for 300-088, 300-089	900-117
Replacement Blades for 300-090	300-004B

Eclipse Tools

Heavy Duty Coaxial Crimping Tool



- Specification : .100" / .359" / .406"
- Crimping cable size : F-59,6,11 & UHF-58,8
- Length : 9"

Description	Part No.
Heavy Duty Coaxial Crimping Tool	902-270


"F" Type Crimper, Non-Ratcheted



- .322 Hex & .255 hex cavities
- Economy crimper for CATV connectors
- Crimps RG59, RG62 and RG6

Description	Part No.
"F" Type crimper, Non-Ratcheted	300-074

Flat Cable Crimp Tool



- Crimps IDC-type connectors onto flat cables
- Connector height range 6-27.5mm(.25-1.08 inches)

Description	Part No.
Flat Cable Crimp Tool	300-011


Economy Wire Ferrule Crimp Tool



- Material: SC45C
- HRC: 45±3
- Including terminal:
 - AWG22x6mm: 40pcs
 - AWG20x6mm: 40pcs
 - AWG18x6mm: 30pcs
 - AWG16x8mm: 20pcs
 - AWG14x7mm: 20pcs

Description	Part No.
Economy Wire Ferrule Crimp Tool	300-016

Crimping Pliers



- UY, UG & UR Connectors
- Built-in stop to protect against overcrimping
- Side cutter
- Insulated handles

Description	Part No.
Crimping Pliers	100-008

Crimper Insulated And Non-Insulated Wire Ferrules



- Fully ratcheted tool
- AWG 20-12
- Single cavity tool
- Omega spring design crimps different size ferrules with no adjustments

Description	Part No.
Crimper Insulated And Non-Insulated Wire Ferrules	300-149

Closed Barrel Contacts



- AWG 26-20
- 4-Indent crimper
- Spring loaded
- D-sub contacts, screw machine version

Description	Part No.
Standard plugs; 6 position & 8 Position	300-015


Wire Ferrule Crimp Tool-Square Crimp



- Crimping range to AWG 28-10
- Square crimp for better ferrule retention

Description	Part No.
Wire Ferrule Crimp Tool-Square Crimp	CP-462

Plier Style Economy Crimper




- For RG59/62/6 F-connectors

Description	Part No.
Plier Style Economy Crimper	300-092

Cutter/Stripper& Crimper


New



- Versatile 7-inch wire cutter/stripper/crimper
- Scissors-action, up-front wire cutting and wire stripping
- Pliers-style nose allows pulling and looping wire
- Red cushion grip handle provides maximum leverage (TPR)
- Quick lock protects precision cutting surfaces when not in use
- Pivot point design assures greater joint strength and adds easy, precise adjustment capability.

Description	Part No.
Cutter/Stripper& Crimper	CP-415

Multi-Purpose Crimping Tool



- Material: S45C
- HRC: 45±3

Description	Application			Part No.
	Strip	Bolt cutter	Crimp	
Multi-Purpose Crimping Tool	10, 12, 14, 16, 18, 20, 22AWG	4-40, 5-40, 6-32, 8-32, 10-32, 10-24	10-16AWG 18-22AWG	902-088


D-Sub, 2-Stage,Open Barrel Crimper



- Non-ratcheted
- 2-Stage crimp (conductor & insulation)
- AWG 20-24-28

Description	Part No.
D-Sub, 2-Stage,Open Barrel Crimper	300-075


Multi-Purpose Crimper



- Crimps a variety of open barrel contacts including solderless lugs and D-sub contacts
- AWG 28-14

Description	Part No.
Multi-Purpose Crimper	300-035

All-In-One Tool



- Wire cutter
- Wire stripper
- Bolt cutter
- Cushion-grips
- Crimper for red, blue & yellow insulated terminals

Description	Application			Part No.
	Strip	Bolt cutter	Crimp	
All-In-One Tool	AWG: 10, 12,14, 16, 18, 20-22	4-40, 6-32, 8-32, 10-24, 10-32	Insulated: 22-18, 16-14, 12-10	100-002
			Non-Insulated: 22-18, 16-14, 12-10 AWG	

Heavy Duty Wire Strippers/Crimpers

New



Item #: CP-412
OAL: 206mm



Item #: CP-413
OAL: 215mm

Eclipse Tools

Part No.	CP-412	CP-413
Wire strip	Stranded wire 24-22, 20, 18, 16, 14, 12 AWG	Stranded wire 26-24, 22-20, 18, 16, 14, 12, 10
	Single wire 22-20, 18, 16, 14, 12, 10 AWG	Single wire 22-20, 18, 16, 14, 12, 10, 8
Bolt cutter	4-40, 5-40, 8-32, 6-32, 10-32, 10-24	4-40, 10-32, 10-24, 8-32, 6-32
Crimp	16-10, 22-18	26-14, 12-10 (Non-insulated terminal) 22-10 (Insulated terminal)
Clamper & cutting	Solid wire	-

Compression Connector Crimp Tool



- Crimps RG59/6/6 Quad F-Compression Connectors.
- Crimps RG7/8/11 Riser F-Compression Connectors.
- Fully adjustable to fit common connector sizes.



Description	Part No.
Compression Connector Crimp Tool	902-265

Compression Connectors Crimp Tool



- Universal tool for all F, BNC, and RCA connectors.
- Works on RG59/6/6Q and large RG7/11 Riser Cable Connectors.

Description	Part No.
RG6/58/59/8/11 F, BNC and RCA Type Compression Connectors	300-156


Compression Connector Crimping Tool



- For F-Type RG 59/6/6 Quad connectors only

Description	Part No.
Compression Connector Crimping Tool	902-245

Adjustable Compression Crimping Tool



- Crimps RG 59/6/6Q compression connectors.
- BNC/RCA and F-Type.



Description	Part No.
Adjustable Compression Tool for F, BNC, RCA Compression Connectors	CP-313

RG6/58/59 Compression Crimper



- Interchangeable heads
- Crimps F-Type, RCA and BNC/TNC connectors
- Crimps RG 6, 58, 59 compression connectors

Description	Part No.
RG6/58/59 Compression Crimper	300-150

Eclipse Tools

Snap Fit Connector Crimper



- Crimps F-Type connector and other brand compression style connectors

Description	Part No.
Snap Fit Connector Crimper (F-Type connectors only)	300-091

Non-Insulated Terminal Crimper

- Ratcheted design
- Crimps solderless, noninsulated terminals
- AWG 22-6
- O.A.L.:11-1/4"



Description	Part No.
Non-Insulated Terminal Crimper	300-055

Ratchet Crimp Tool for Non-Insulated Terminals




- Material: Frame S45C
- Die: SK-5
- O.A.L.:13-3/8"



Description	Application	Part No.
Ratchet Crimp Tool for Non-Insulated Terminals	AWG: 12-10, 8, 6, 4	902-089

Heavy Duty Solderless Lug Crimper

- Two Capacity plates-Aluminum and Copper
- Crimps terminals from AWG 8 to 250 MCM
- Adjustable w/knob on top of tool
- O.A.L. : 22-1/2"



Description	Part No.
Heavy Duty Solderless Lug Crimper	300-107

Compression Connector Crimp Kit

Contents:

- Waterproof Connector Crimping Tool
- Round Cable Cutter
- Wire Stripper Tool
- F Connector for RG6(Black) 10pc



Comes in Handy Carrying Case with Foam Insert



New

Description	Part No.
Compression Connector Crimp Kit	PK-3022




CUTTERS



www.eclipsetools.com


- High grade alloy steel
- Induction hardened cutting edges
- Double leaf springs
- Hot drop forged
- Mirror polished surface
- Oil hardened & tempered
- Hot-formed box joints

4-1/2" Semi-Flush Diagonal Cutter




Description	Application	Part No.
4-1/2" Semi-Flush Diagonal Cutter	Hard steel: 20 AWG, Soft steel: 16 AWG Copper: 12 AWG	200-056

4-1/2" Full-Flush Straight Side Cutter




Description	Application	Part No.
4-1/2" Full-Flush Straight Side Cutter	Hard steel: 20 AWG, Soft steel: 16 AWG Copper: 12 AWG	200-059

4-1/2" Full-Flush Diagonal Cutter




Description	Application	Part No.
4-1/2" Full-Flush Diagonal Cutter	Hard steel: 20 AWG, Soft steel: 16 AWG Copper: 12 AWG	200-057

5" Flush Oblique Cutter Slim Tip



Description	Application	Part No.
5" Flush Oblique Cutter Slim Tip	Hard steel: 20 AWG, Soft steel: 18 AWG Copper: 14 AWG	200-060

4-1/2" Slim Full-Flush Diagonal Cutter



Description	Application	Part No.
4-1/2" Slim Full-Flush Diagonal Cutter	Hard steel: 20 AWG, Soft steel: 16 AWG Copper: 14 AWG	200-058



5" Side Cutting Plier



Description	Application	Part No.
5" Side Cutting Plier	Hard steel: 20 AWG, Soft steel: 14 AWG Copper: 12 AWG	200-067

5" Micro Cutter

Description	Part No.
5" Micro Cutter	902-011


5" Micro Cutter

Unit: inch

Description	Application	Part No.
5" Micro Cutter	Copper 1.3mm	200-092

5" Economy Flush Cutter

- Spring loaded, flush cut
- Cushioned grips
- Diagonal blade orientation
- Good for PC board lead trimming




Unit: inch

Description	Application	Part No.
5" Economy Flush Cutter	Copper: 14 AWG	200-002

5" "ESD Safe" Micro Cutter

- Spring loaded handles
- Cutting copper and other soft leads
- Dissipative handles




Unit: inch

Description	Application	Part No.
5" "ESD Safe" Micro Cutter	Copper: 16 AWG	200-040

5" Precision Flush Cutter

- Micro tips, good for precision work




Unit: inch

Description	Application	Part No.
5" Precision Flush Cutter	Copper: 16 AWG	200-071

5" Heavy Duty "ESD Safe" Cutter


W/Safety clip

- Heavy duty blades and springs
- Spring loaded handles
- Dissipative handles
- Cutting copper and other soft leads
- Safety Clip Prevents Flying Leads



Unit: inch

Description	Application	Part No.
5" Heavy Duty "ESD Safe" Cutter	Copper: 12 AWG	200-041
With safety clip		200-082


5" Micro Cutter

Unit: inch

Description	Application	Part No.
5" Micro Cutter	Copper: 14 AWG, Soft steel: 21 AWG	200-088

5" Clean Cut Micro Nipper


- This nipper is designed for delicate work.



Unit: inch

Description	Application	Part No.
5" Clean Cut Micro Nipper	Cutting capacity: 20 AWG, soft wire	200-083

5" Cutting Plier




Unit: inch



Description	Application	Part No.
5" Cutting Plier	Copper: 1.3mm	PM-251

5" Micro Cutting Plier

- Material: SK5
- HRC: 50±3




Unit: inch




Description	Application	Part No.
5" Micro Cutting Plier	Soft steel: AWG 20 Copper: AWG 14	902-075

4 1/2" Precision Cutting Plier

- Material: S60C
- HRC: 55~60 (Cutting edge)




Unit: inch



Description	Application	Part No.
4 1/2" Precision Cutting Plier	Copper: AWG 14	902-078

5" Micro Cutting Plier

- Material: SK5
- HRC: 50±3




Unit: inch



Description	Application	Part No.
5" Micro Cutting Plier	Soft steel: AWG 20 Copper: AWG14	902-076

7" Plastic Cutting Plier

- Material: S55C
- HRC: 58±3 (Cutting edge)



Unit: inch




Description	Application	Part No.
7" Plastic Cutting Plier	only for plastic cutting	902-049



The pliers are for cutting plastic only. Do not use them to cut any other types of material.

5" Micro Cutting Plier

- Material: SK5
- HRC: 50±3



Unit: inch



Description	Application	Part No.
5" Micro Cutting Plier	Copper: AWG 14	902-077

All Purpose Snip



Cut cloth, carpet, linoleum, leather, cardboard, tin plate, branches, foam rubber and more. Stainless steel spring and blades resist rust and corrosion. Positive safety latch.

Description	Part No.
All Purpose Snip	902-082

Flat Cable Cutter



- Material: AISI 420
- Handle: P.P.+T.P.R
- Flat Blade Geometry

Description	Part No.
Flat Cable Cutter	902-083

Round Cable Cutter



Great for Coax and
100 Pair Cable

- Material: AISI 420
- HRC: P.P. + T.P.R
- Rounded Blade Geometry
- Comfort Grip

Description	Part No.
Round Cable Cutter	902-084

2-in-1 Wire Stripper/Cutter



- Great for PC Board and Cable Assy
- OAL: 5"

Round Cable Cutter





- For large wires up to 2/0
- Up to 100 Pair cable
- Return spring
- Insulated handles
- OAL: 8-1/2"

Description	Application	Part No.
2-in-1 Wire Stripper/Cutter	Stripper 0.4~1.6mm ² (26~14 AWG)	200-080

Eclipse Tools

Description	Application	Part No.
Round Cable Cutter	Thick wire up to 2/0 (70mm ²) cable, 100 pair group telephone cable	200-046


4-1/2" Diagonal Cutter



- Spring loaded handles
- Smooth cushion grip
- Cuts copper & other soft leads

Description	Application	Part No.
4-1/2" Diagonal Cutter	Soft steel: 16 AWG Copper: 14 AWG	200-037


5" Diagonal Cutters-two color



Unit: inch

Description	Application	Part No.
5" Diagonal Cutters-two color	Copper: 1.6mm	200-089


5" Heavy Duty Cutter



Unit: inch

Description	Application	Part No.
5" Heavy Duty Cutter	Piano wire 16 AWG	200-087

6" Diagonal Cutter



Unit: inch

- Smooth Cushion grip
- Cutting copper & other soft leads
- Chrome-Vanadium blades

Description	Application	Part No.
6" Diagonal Cutter Eclipse Tools	Soft steel: 12 AWG Copper: 10 AWG	200-038

6-1/2" Cable Cutter


Best Value



- Cuts wire and cable up to 0.40" diameter
- Coaxial cable up to RG-9/U
- Spring loaded
- For copper and aluminum wire only

Description	Application	Part No.
6-1/2" Cable Cutter	Multi-conductor cable up to 0.5"(12.7mm) Stranded wire up to 8 AWG(10mm2)	200-015

6" 8" And 10" Cable Cutter



- Unique jaw shape keeps cable round during cutting
- Forged steel high quality blades

Description	Application		Part No.
	Copper cable	Aluminum cable	
6" Cutter	4 AWG solid, 2 AWG stranded 2/0 flexible	2/0 stranded	200-068
8" Cutter	3 AWG flexible	3 AWG stranded	200-013
10" Cutter	2 AWG flexible	2 AWG stranded	200-069

Wire Rope Cutter




- Cuts metal wires, rods and ropes
- Compare to Klein 63016
- O.A.L.: 7-1/2"

Description	Application	Part No.
Wire Rope Cutter	Cutting capacities: 0.16"(4mm) Wire rope 0.06"(1.5mm) Spring wire	200-063

8" Side Cutting Plier



New



Unit: inch

Description	Application	Part No.
8" Side Cutting Plier	Cutting edge: HRC55 $\pm$ 3° Material: S55C Hardness: HRC40°~45°	902-246

Ratchet Cable Cutter



Item #: 902-258

New



Item #: 902-259

New



- Cuts cable up to 750MCM
- Quick release knob for easy blade back out
- Handle locks for convenient tool storage
- For copper and Aluminum Cables only not for cutting Steel

Description	Part No.
Ratchet Cable Cutter	902-062
Moving blade for 902-062	902-258
Stationary blade for 902-062	902-259


Heavy Duty Cable Cutter

- Ratcheted w/safety release
- Comfortable handles
- For aluminum and soft Copper cables up to 1.25" - 500 MCM



Description	Application	Part No.
Heavy Duty Cable Cutter	1.25" Copper & Aluminum cable	200-006
Replacement Blade (stationary)		200-035
Replacement Blade (moving)		200-034

Heavy Duty Cable Cutter



- Rubber cushioning in handle
- Heavy duty construction

Description	Application	Part No.
Heavy Duty Cable Cutter	Copper and aluminum cables up to 500 MCM	200-043

Eclipse Tools

Finger Duct Cutter



- For finger duct only.

Description	Part No.
Finger Duct Cutter	200-086

Ratchet PVC Pipe Cutter



- Ratcheted design - Easy on hands

Description	Application	Part No.
Ratchet PVC Pipe Cutter	Cuts up to 1.25" diameter PVC pipe	200-039
Replacement Blade		200-045

Ratchet PVC Pipe Cutter



- Ratcheted

Description	Application	Part No.
Ratchet PVC Pipe Cutter	Cuts up to 2 inch Diameter PVC Pipe	200-076
Replacement Blade		900-211

PVC Pipe Cutter (Economy type)

Best Value


New



Description	Part No.
PVC Cutter(Economy type)	SR-008




PLIERS



www.eclipse tools.com

5" Needle-Nosed Plier (serrated jaw)



Unit: inch

Description	Part No.
5" Needle-Nosed Plier serrated jaw	100-011


5-1/2" Bent-Nosed Plier (smooth jaw)



Unit: inch

Description	Part No.
5-1/2" Bent-Nosed Plier smooth jaw	100-014


6" Needle-Nosed Plier slim (serrated jaw)



Unit: inch

Description	Part No.
6" Needle-Nosed Plier slim serrated jaw	100-012

5-1/2" Flat-Nosed Plier (smooth jaw)



Unit: inch

Description	Part No.
5-1/2" Flat-Nosed Plier smooth jaw	100-015

5-1/2" Needle-Nosed Plier (smooth jaw)



Unit: inch

Description	Part No.
5-1/2" Needle-Nosed Plier smooth jaw	100-013

5-1/2" Round-Nosed Plier



Unit: inch

Description	Part No.
5-1/2" Round-Nosed Plier	100-016

7-1/2" Long-Nosed Flat Blade Plier



Unit: inch

Description	Part No.
7-1/2" Long-Nosed Flat Blade Plier	100-006


6" Needle-Nosed Plier (serrated jaw)



Unit: inch

Description	Part No.
6" Needle-Nosed Plier serrated jaw	100-017

5" Long-Nosed Plier (serrated jaw)



Description	Part No.
5" Long-Nosed Plier serrated jaw	100-025

5" Long-Nosed Plier (Serrated jaw)




Description	Part No.
5" Long-Nosed Plier Serrated jaw	100-024

6" Needle-Nosed Plier



Description	Part No.
6" Needle-Nosed Plier	100-042


5" Flat-Nosed Plier



Description	Part No.
5" Flat-Nosed Plier	100-044

5" Needle-Nosed Plier


- Micro finish
- Spring-loaded handles
- Smooth cushion grip
- Bending and cutting copper & other soft leads
- Serrated jaws



Description	Part No.
5" Needle-Nosed Plier	100-003

5" Bent-Nosed Plier

- Micro finish
- Spring-loaded handles
- Smooth cushion grip
- Bending copper & other soft leads
- Serrated jaws



Description	Part No.
5" Bent-Nosed Plier	100-004

4-1/2" Extra Long and Slim Plier

Item #: PM-252



Item #: PM-254




Description	Material	HRC	OAL	Part No.
4-1/2" Bent Nose Plier	AISI420	HRC43~46°	4.6"	PM-252
4-1/2" Long Nose Plier	AISI420	HRC43~46°	4.6"	PM-254

• Extra long and slim design is the best choice for accurate handling of small objects in inaccessible areas.

Eclipse Tools

5-1/2" Dual Color Long-Nosed Plier



Unit: inch

Description	Part No.
5-1/2" Dual Color Long-Nosed Plier	100-041

6" Long-Nosed Plier



Unit: inch

Description	Part No.
6" Long-Nosed Plier	100-046

5-1/2" Dual Color Flat-Nosed Plier



Unit: inch

Description	Part No.
5-1/2" Dual Color Flat-Nosed Plier	100-043

5" "ESD Safe" Plier



Unit: inch

- Serrated jaws
- Spring-loaded handles
- Bending copper & other soft leads
- Dissipative handles

Description	Part No.
5" "ESD Safe" Plier	100-007


5-1/2" Dual Color Bent-Nosed Plier



Unit: inch

Description	Part No.
5-1/2" Dual Color Bent-Nosed Plier	100-045

6" Needle-Nosed Plier




Unit: inch

- Smooth cushion grip
- Bending and cutting copper & other soft leads
- Serrated jaws

Description	Application	Part No.
6" Needle-Nosed Plier	Soft steel: 2.0mm Copper: 2.6mm	100-021

5-1/2" Long Nosed Plier




Unit: inch

Description	Part No.
5-1/2" Long Nosed Plier	100-040

Eclipse Tools

5" Extra Long Nose Plier



Unit: inch

- Material: S60C
- HRC: 55-60 (Cutting edge)

Description	Application	Part No.
5" Extra Long Nose Plier	Soft steel: AWG 16 Copper: AWG 12	902-079

Slip-Channel Pump Plier


- Insulated handles for comfort
- Channel-joint allows wider variety of size accommodation



Description	Part No.
Slip-Channel Pump Plier 8"	100-030
Slip-Channel Pump Plier 10"	100-031
Slip-Channel Pump Plier 12"	100-032

Slip-Joint Plier

- Insulated handles for comfort
- Slip-joint allows wider variety of size accommodation



Description	Part No.
Slip-Joint Plier 6"	100-033
Slip-Joint Plier 8"	100-034
Slip-Joint Plier 10"	100-036

9" Heavy Duty Lineman's Plier

- Heavy duty cutter
- Plastic dipped handles
- Material: CR-V steel
- Cut Piano wire up to AWG 10




Unit: inch

Description	Application	Part No.
9" Heavy Duty Lineman's Plier	Steel wire 10 AWG	100-023

8" Lineman's Plier

- Cushion grip
- Built-in cutter
- Heavy duty steel construction



Unit: inch

Description	Application	Part No.
8" Lineman's Plier	soft steel: 10 AWG Copper: 8 AWG	100-005

Eclipse Tools

5" Locking Plier



Item #: 100-026



Item #: 100-027



Item #: 100-028



Item #: 100-047



Item #: 100-048

- Industrial grade
- Adjustable locking mechanism
- Drop-forged alloy steel
- Heat treated for strength and durability

Description	Part No.
5" Locking Plier	100-026
6" Locking Plier	100-027
7" Locking Plier	100-028
10" Locking Plier	100-047
12" Locking Plier	100-048

Strain Relief Bushing Assembly Tool

• O.A.L. : 6-1/2"




Description	Part No.
Strain Relief Bushing Assembly Tool	300-151

8" Side Cutter w/crimper



Description	Part No.
8" Side Cutter w/crimper	100-037

9" Heavy Duty Long-Nosed Plier



Description	Part No.
9" Heavy Duty Long-Nosed Plier	100-038

9-1/2" Multi-Crimp Tool

• AWG 22-10 non-insulated terminals.



Description	Part No.
9-1/2" Multi-Crimp Tool	100-039

All Purpose - 8" Plier

- Cutter/pliers
- Chrome vanadium steel
- Screw cutter



Description	Application	Part No.
All Purpose- 8" Plier	Multi-crimpers for AWG 14-10 & AWG 10-6 wires Stripper AWG 18, 16, 14, 12, 10	100-001

6" Snap Ring Pliers Set

- Straight, 90° and 45° heads
- Works with both inner and outer style clips



Description	Part No.
6" Snap Ring Pliers Set	100-022

Eclipse Tools



SCISSORS



www.eclipsetools.com

Electrician's Scissor

- Designed for use in telephone and electrical service applications
- Scraper and file on side edge of blade
- Cut up to 16 AWG solid wire and 12 AWG stranded wire
- Cut length: 1.85"
- Overall length: 5.7"



Double stripping notches strip 19 and 23 AWG wire.



Easy to cut



Description	Part No.
Electrician's Scissor	100-049

Electrician's Scissor

- V-notches for stripping wire

Description	Part No.
Electrician's Scissor	100-009



Fiber Kevlar Scissor

- Used to cut fiber optic cable Aramid/Kevlar threads

Description	Part No.
Fiber Kevlar Scissor	100-035



Aviation Snips

- Insulated handles for comfort
- Right, Left and Straight models
- Cuts Aluminum and Steel sheet metal




Left cutting Item #: 200-073 Straight cutting Item #: 200-075 Right cutting Item #: 200-074

Description	Part No.
Aviation Snips Left Cutting	200-073
Aviation Snips Right Cutting	200-074
Aviation Snips Straight Cutting	200-075

Eclipse Tools





STRIPPERS



www.eclipsetools.com

Adjustable Cutter / Stripper

- Adjusts with a screwdriver
- High carbon steel
- Precision ground cutting surface



Description	Part No.
Adjustable Cutter/Stripper	200-007
Adjustable Cutter/Stripper(Without spring)	200-007W

Precision Wire Stripper

- Plier nose
- Cutter jaws
- Soft handles
- Spring return



Description	Part No.
Cutter/Stripper AWG 20, 18, 16, 14, 12 & 10	200-010
Cutter/Stripper AWG 30, 28, 26, 24, 22 & 20	200-001
Cutter/Stripper AWG 16, 14, 12, 10, 8	902-090

Wire Stripper-Cutter w/Spring



Description	Part No.
Wire Stripper-Cutter w/Spring	200-085

Fiber Optic Stripper

- Nick-Free
- Screw for fine adjustments
- Spring Loaded Handles
- Strips 900 um buffer
- Strips 2-3 mm jacket
- Strips 125 um Acrylate



Description	Part No.
Fiber Optic Stripper	200-047

Multi-Function Heavy Duty Stripper

- Insulated terminals -22-10 AWG
- Non-insulated terminals -22-10 AWG
- Auto ignition terminals
- Built-in cutter
- Adjustable stopper
- Micro adjustment
- Strips AWG 24-10
- Crimps Lugs and Terminals



Description	Part No.
Multi-Function Heavy Duty Stripper	200-070


Economy Self-Adjusting Stripper

- Lower Cost Version of the 200-070 Heavy Duty Stripper



Description	Part No.
Economy Self-Adjusting Stripper	200-072

Wire Stripper



Description	Application	Part No.
Wire Stripper	Strips flexible cable from AWG 24-12	200-091

Adjustable Stripper

- Dial sets tool for accurate stripping of AWG 26-12 wire, for individual or repetitive stripping.
- Spring opening for fast, easy use.
- Lock closes stripper to protect hardened cutting edge.
- Vinyl cushion handle.



Description	Part No.
Adjustable Stripper	902-247

Wire Stripping Tool

- Strips PVC, Teflon & Silicone wires
- Aluminum die cast



Description	Application	Part No.
Wire Stripping Tool	Strips AWG 22, 16, 14, 12, 10 & 8 wire	200-003

Multi-Function Wire Stripper


- Silver satin cable
- 26-16 AWG wire
- RG-58/59/62
- Strips and Cuts



Description	Part No.
Multi-Function Wire Stripper	200-064

Universal Stripping Tool


- Strips and cuts round and flat multi-conductor cable including UTP cable



Description	Part No.
Universal Stripping Tool	200-016
Replacement Blade for 200-016	900-117

Coax Stripper

1. Slot "A" for stripping center core.
 2. Slot "B" for stripping outer jacket. Rotating each 3 to 5 times in clockwise direction (as arrow)
- Strips cables in 2 easy steps.



Description	Application	Part No.
Coax Stripper	For RG-58,59,62,6	200-090

Universal Fiber Optic Cable Stripper

- For stripping fiber optic cable .010" and .0125" diameter



Description	Part No.
Universal Fiber Optic Cable Stripper	200-055

Eclipse Tools

Rotary Cable Slitter

- Slits/strips round cables
- Adjustable cutting depth
- Blade swivels for longitudinal/spiral cuts



Description	Part No.
Range 0.18"~1.0" diameter	200-009
Range 1.0"~1.4" diameter	200-048
Replacement Blade	200-036

Coax Stripper

- Clothespin design
- Strip configuration for RG6, 58 and 59
- Adjustable blades



Description	Part No.
Coax Stripper	200-084

Rotary Coaxial Cable Stripper

- For RG-58/59/62/6 cable
- 2-Blade model
- Strips 4, 8, 12mm lengths
- Great for F, BNC and RCA Compression Connectors



Description	Part No.
Rotary Coaxial Cable Stripper	200-004
Replacement Blade (Set of 6)	900-026

Rotary Coaxial Cable Stripper

- For RG-58/59
- 3-Blade model
- Strips 4, 8, 12mm lengths



Description	Part No.
Rotary Coaxial Cable Stripper	200-005
For big cable O.D. around 10.5mm such as RG213	200-081
Replacement Blade (Set of 6)	900-027

Rotary Coax Stripper

- 2-Blade Model



Description	Part No.
Rotary Coaxial Stripper (RG-58/59/62)	200-049
Rotary Coaxial Stripper (RG-59/62/6)	200-050
Replacement Blades (Set of 6)	900-027

Rotary Coax Stripper

- 3-Blade model RG-59/62/6



Description	Part No.
Rotary Coax Stripper	200-051
Replacement Blade (Set of 6)	900-027

Rotary Coaxial Cable Stripper

- New shape
- 2 or 3 Step strips without adjustment
- Ethernet, Thinnet, RG-62 and RG-59 and others
- Strip Lengths: .315 and .157
- RG58/59/62/6/6Q

Description	Part No.
Rotary Coaxial Cable Stripper	200-065



Eclipse Tools

Economy UTP Stripper



- Simple to use
- Multi-station stripper
- Rotary action operation
- 110 Type punchdown blade in tip

Item #: 200-042-100

100 pc Display Jug
for Distributor's
counter



Description	Part No.
Economy UTP Stripper	200-042
Economy UTP Stripper (100 pcs/jug)	200-042-100


Universal Stripping Tool

Best Value



- Strips flat telephone cable
- Cable cutter function
- Strips RG-59/6/11/7 coaxial cable
- Strips outer jacket of UTP and STP cable and CAT 5 round telephone cable
- Standard .25 X .25 strip length for coax

New



Item #: 902-268

Coax Flaring Tool

One end for this tool is for flaring the braid and the other for screwing on a twist-on F-Connector to the cable.

- Length: 4.3x2.4x0.4" (110x60x9.5mm)
- Material: 12L14
- Finish: Nickel Plating



New

New



Item #: 902-269

Description	Part No.
Coax Flaring Tool	MS-3207

Description	Part No.
Universal Stripping Tool	902-229
Cassette	902-268
Replacement Blade Set = 4pcs	902-269

Eclipse Tools



CONNECTORS



www.eclipsetools.com

Twist-On Wire Connectors

- Excellent spring retention in housing
- Maintain secure grip on wires
- UL 486C listed and CSA certified
- UL 94V-2 flame retardant plastic
- 1000V rated in fixtures and signs

Standard Style			
Description	Package Quantity	Part No.	Color
	300V AWG 22-14 Min 2 #22 - Max 1 #14 w/1 #20	25 pc. Retail Pack	Gray
		100 pc Box	
		1,000 pc Bag	
	300 V AWG 22-14 Min 2 # 22 - Max 3 #16	25 pc. Retail Pack	Blue
		100 pc Box	
		1,000 pc Bag	
	600 V AWG 22-14 Min 1 #18 w/1 # 20 - Max 4 #16 w/1 #20	25 pc. Retail Pack	Orange
		100 pc Box	
		500 pc Bag	
	600V AWG 22-10 Min 3 #20 - Max 1 #10 w/2 #14 w/1 #16	25 pc. Retail Pack	Yellow
		100 pc Box	
		500 pc Bag	
	600 V AWG 22-8 Min 3 #18 - Max 3 #10	25 pc. Retail Pack	Red
		100 pc Box	
		500 pc Bag	

Winged Style			
Description	Package Quantity	Part No.	Color
	600V AWG 18-10 Min 2 #18 - Max 3 #12	25 pc Retail Pack	Yellow
		100 pc Box	
		500 pc Bag	
	600V AWG 22-8 Min 2 #22 - Max 3 #10	25 pc Retail Pack	Tan
		100 pc Box	
		500 pc Bag	
	600V AWG 18-8 Min 3 #16 - Max 5 #12	25 pc Retail Pack	Red
		100 pc Box	
		500 pc Bag	
	600V AWG 14-6 Min 2 #10 w/1#12 - Max 1 #8 w/3#10	15 pc Retail Pack	Blue
		50 pc Box	
		5x100 pc Bag	

Slim-Line Style			
Description	Package Quantity	Part No.	Color
	600V AWG 22-10 Min 2 #18 - Max 3 #12	25 pc. Retail Pack	Yellow
		100 pc Box	
		500 pc Bag	
	600 V AWG 22-8 Min 2 # 18 - Max 5 #12	25 pc. Retail Pack	Red
		100 pc Box	
		500 pc Bag	

Telecom Splices

- Use Crimp Tool P/N 100-008

UR AWG 26-20
Eclipse Tools

UG AWG 19-26

UY AWG 26-22

- Silicone gel filled for protection from elements

Compression Style Connectors-F, RCA & BNC Type



Description	Bag Q'ty	Part No.
F connector for RG6/U (Black)	100 pcs	705-001-BK
F connector for RG6/U (Black)	50 pcs	705-001-BK-50
F connector for RG6/U (Black)	25 pcs	705-001-BK-25
F connector for RG6 Quad (Blue)	100 pcs	705-002-BU
F connector for RG6 Quad (Blue)	50 pcs	705-002-BU-50
F connector for RG6 Quad (Blue)	25 pcs	705-002-BU-25
F connector for RG59/U (Black)	100 pcs	705-003-BK
F connector for RG59/U (Black)	50 pcs	705-003-BK-50
F connector for RG59/U (Black)	25 pcs	705-003-BK-25
RCA connector for RG6/U (Green)	100 pcs	705-004-GN
RCA connector for RG6/U (Green)	50 pcs	705-004-GN-50
RCA connector for RG6/U (Green)	25 pcs	705-004-GN-25
RCA connector RG6/U (Blue)	100 pcs	705-004-BU
RCA connector RG6/U (Blue)	50 pcs	705-004-BU-50
RCA connector RG6/U (Blue)	25 pcs	705-004-BU-25
RCA connector for RG6/U (Black)	100 pcs	705-004-BK
RCA connector for RG6/U (Black)	50 pcs	705-004-BK-50
RCA connector for RG6/U (Black) 50 pc poly bag	25 pcs	705-004-BK-25
RCA connector RG6/U (Red) 100 pc poly bag	100 pcs	705-004-RD
RCA connector RG6/U (Red) 50 pc poly bag	50 pcs	705-004-RD-50
RCA connector RG6/U (Red) 25 pc poly bag	25 pcs	705-004-RD-25
RCA connector RG6/U (Yellow) 100 pc poly bag	100 pcs	705-004-YL
RCA connector RG6/U (Yellow) 50 pc poly bag	50 pcs	705-004-YL-50
RCA connector RG6/U (Yellow) 25 pc poly bag	25 pcs	705-004-YL-25
RCA connector RG6/U (White) 100 pc poly bag	100 pcs	705-004-WH
RCA connector RG6/U (White) 50 pc poly bag	50 pcs	705-004-WH-50
RCA connector RG6/U (White) 25 pc poly bag	25 pcs	705-004-WH-25
RCA connector RG59/U (Black) 100 pc poly bag	100 pcs	705-005-BK
RCA connector RG59/U (Black) 50 pc poly bag	50 pcs	705-005-BK-50
RCA connector RG59/U (Black) 25 pc poly bag	25 pcs	705-005-BK-25
BNC connector for RG6/U (Black) 100 pc poly bag	100 pcs	705-006-BK
BNC connector for RG6/U (Black) 50 pc poly bag	50 pcs	705-006-BK-50
BNC connector for RG6/U (Black) 25 pc poly bag	25 pcs	705-006-BK-25
BNC connector for RG6 Quad (Blue) 100 pc poly bag	100 pcs	705-007-BU
BNC connector for RG6 Quad (Blue) 50 pc poly bag	50 pcs	705-007-BU-50
BNC connector for RG6 Quad (Blue) 25 pc poly bag	25 pcs	705-007-BU-25
BNC connector for RG59/U (Black) 100 pc poly bag	100 pcs	705-008-BK
BNC connector for RG59/U (Black) 50 pc poly bag	50 pcs	705-008-BK-50
BNC connector for RG59/U (Black) 25 pc poly bag	25 pcs	705-008-BK-25

Description	Package Quantity	Part No.
UY Connectors	1,000 Pc. Bag	703-001
UY Connectors	100 Pc. Retail Pack	703-003
UY Connectors	25 Pc. Retail Pack	703-005

Description	Package Quantity	Part No.
UR Connectors	1,000 Pc. Bag	703-002
UR Connectors	100 Pc. Retail Pack	703-004
UR Connectors	25 Pc. Retail Pack	703-006

Description	Package Quantity	Part No.
UG Connectors	1,000 Pc. Bag	703-007
UG Connectors	100 Pc. Retail Pack	703-008
UG Connectors	25 Pc. Retail Pack	703-009

Modular Plugs

ALL OF OUR SOLID-WIRE MODULAR PLUGS ARE "THREE-PRONG" STYLE



Pos/Contacts	Cable Type	Wire Type	Premium Grade 50 uin Gold		Economy Grade Thin Gold Flash	
			50 Pc Pack	1,000 Pc Bag	50 Pc Pack	1,000 Pc Bag
4P4C (RJ11)	Flat	Stranded	702-001	702-030	702-059	702-083
	Flat	Solid	702-014	702-043	702-072	702-096
6P2C	Flat	Stranded	702-002	702-031	702-060	702-084
	Round	Stranded	702-003	702-032	702-061	702-085
	Flat	Solid	702-015	702-044	702-073	702-097
	Round	Solid	702-016	702-045	702-074	702-098
6P4C (RJ11)	Flat	Stranded	702-004	702-033	702-062	702-086
	Round	Stranded	702-005	702-034	702-063	702-087
	Flat	Solid	702-017	702-046	702-075	702-099
	Round	Solid	702-018	702-047	702-076	702-100
6P6C (RJ12)	Flat	Stranded	702-006	702-035	702-064	702-088
	Round	Stranded	702-007	702-036	702-065	702-089
	Flat	Solid	702-019	702-048	702-077	702-101
	Round	Solid	702-020	702-049	702-078	702-102
8P8C (RJ45) CAT 5e	Flat	Stranded	702-008	702-037	702-066	702-090
	Round	Stranded	702-009	702-038	702-067	702-091
	Flat	Solid	702-021	702-050	702-079	702-103
	Round	Solid	702-022	702-051	702-080	702-104
8P8C AMP STYLE CAT 5e	Flat	Stranded	702-010	702-039	702-068	702-092
	Round	Stranded	702-011	702-040	702-069	702-093
	Flat	Solid	702-023	702-052	702-081	702-105
	Round	Solid	702-024	702-053	702-082	702-106
10P10C	Flat	Stranded	702-012	702-041	702-070	702-094
	Round	Stranded	702-013	702-042	702-071	702-095
To Select Proper Plug	Step 1 Pick the number of positions in block and number of pins loaded in block.					
	Step 2 Choose flat or round cable					
	Step 3 Choose Stranded or Solid conductors (wire)					
	Step 4 Choose Premium Grade or Economy Grade - Gold thickness is only difference					
	Step 5 Choose Pack Quantity (retail pack of 50 pcs or Bulk bag of 1,000 pcs.)					
	Step 6 If you need Snagless Boots, choose from below:					


Color	50 Pc. Retail Pack	1,000 Pc. Bulk Bag
Blue	702-025	702-054
Gray	702-026	702-055
Yellow	702-027	702-056
Red	702-028	702-057
Green	702-029	702-058




INSULATED WIRE FERRULES

Part #	AWG	mm ²	color	d1	d2	L1	L2	Bag Q'ty
701-088	28-26	0.14	Gray	0.7	1.6	10.6	6	500
701-025	24	0.25	Lt.Blue	0.8	1.8	10.8	6	500
701-104	24	0.25	Yellow	0.8	1.8	10.8	6	500
701-007	24	0.25	Lt.Blue	0.8	1.8	12.8	8	500
701-026	22	0.34	Turquoise	0.9	2.0	10.8	6	500
701-027	22	0.34	Turquoise	0.9	2.0	12.8	8	500
701-008	22	0.5	Orange	1.1	2.6	12.5	6	500
701-097	22	0.5	White	1.1	2.6	14.5	8	500
701-028	22	0.5	Orange	1.1	2.6	14.5	8	500
701-010	22	0.5	Orange	1.1	2.6	16.5	10	500
701-029	20	0.75	White	1.3	2.8	12.5	6	500
701-111	20	0.75	Gray	1.3	2.8	14.5	8	500
701-011	20	0.75	White	1.3	2.8	14.5	8	500
701-013	20	0.75	White	1.3	2.8	16.5	10	500
701-131	20	0.75	Gray	1.3	2.8	16.5	10	500
701-030	20	0.75	White	1.3	2.8	18.5	12	500
701-031	18	1.0	Yellow	1.5	3.0	12.5	6	500
701-132	18	1.0	Red	1.5	3.0	12.5	6	500
701-014	18	1.0	Yellow	1.5	3.0	14.5	8	500
701-099	18	1.0	Red	1.5	3.0	14.5	8	500
701-023	18	1.0	Yellow	1.5	3.0	16.5	10	500
701-130	18	1.0	Red	1.5	3.0	16.5	10	500
701-032	18	1.0	Yellow	1.5	3.0	18.5	12	500
701-117	18	1.0	Red	1.5	3.0	18.5	12	500
701-016	16	1.5	Red	1.8	3.5	14.5	8	500
701-100	16	1.5	Black	1.8	3.5	14.5	8	500
701-024	16	1.5	Red	1.8	3.5	16.5	12	500
701-122	16	1.5	Black	1.8	3.5	16.5	10	500
701-033	16	1.5	Red	1.8	3.5	24.5	18	200
701-101	16	1.5	Black	1.8	3.5	24.5	18	500
701-022	14	2.5	Blue	2.3	4.2	15.0	8	500
701-102	14	2.5	Gray	2.3	4.2	15.0	8	500
701-034	14	2.5	Blue	2.3	4.2	19	12	500
701-113	14	2.5	Gray	2.3	4.2	19	12	500
701-019	14	2.5	Blue	2.3	4.2	25	18	200
701-035	12	4.0	Gray	2.9	4.8	16	9	200
701-036	12	4.0	Gray	2.9	4.8	17	10	200
701-037	12	4.0	Gray	2.9	4.8	25	18	100
701-038	10	6.0	Black	3.6	6.3	20	12	100
701-085	10	6.0	Yellow	3.6	6.3	20	12	100
701-020	10	6.0	Black	3.6	6.3	26	18	100
701-086	8	10	Red	4.6	7.6	21.5	12	100
701-039	8	10	Ivory	4.6	7.6	21.5	12	100
701-040	8	10	Ivory	4.6	7.6	27.5	18	100
701-087	6	16	Blue	6	8.8	22.5	12	100
701-121	6	16	White	6	8.8	22.5	12	100
701-041	6	16	Green	6	8.8	22.5	12	100
701-021	6	16	Green	6	8.8	28.5	18	100
701-042	4	25	Brown	7.5	11.2	29	16	50
701-133	4	25	Black	7.5	11.2	31	18	50
701-043	4	25	Brown	7.5	11.2	35	22	50
701-044	2	35	Beige	8.4	11.2	30	16	25
701-045	2	35	Beige	8.4	12.7	39	25	25
701-046	1/0	50	Olive	10.4	15	36	20	25


INSULATED WIRE FERRULES



UNINSULATED WIRE FERRULES



TWIN WIRE FERRULES



Part#701-998

UNINSULATED WIRE FERRULES

Part #	AWG	mm ²	d1	d2	L1	Bag Q'ty
701-001	24	0.25	0.7	1.65	5	1000
701-047	20	0.5	1.0	2.1	6	1000
701-048	20	0.5	1.0	2.1	10	1000
701-002	18	0.8	1.2	2.3	6	1000
701-049	18	0.8	1.2	2.3	10	1000
701-050	18	1.0	1.4	2.5	6	1000
701-003	18	1.0	1.4	2.5	10	1000
701-051	16	1.5	1.7	2.8	7	1000
701-004	16	1.5	1.7	2.8	10	1000
701-052	16	1.5	1.7	2.8	12	1000
701-053	16	1.5	1.7	2.8	18	1000
701-054	14	2.5	2.2	3.4	7	1000
701-005	14	2.5	2.2	3.4	10	1000
701-055	14	2.5	2.2	3.4	12	1000
701-056	14	2.5	2.2	3.4	18	1000
701-057	12	4.0	2.8	4	9	500
701-006	12	4.0	2.8	4	12	1000
701-058	12	4.0	2.8	4	15	500
701-059	12	4.0	2.8	4	18	500
701-060	10	6.0	3.5	4.7	10	500
701-061	10	6.0	3.5	4.7	12	500
701-062	10	6.0	3.5	4.7	15	500
701-063	10	6.0	3.5	4.7	18	500
701-064	8	10.0	4.5	5.8	12	250
701-065	8	10.0	4.5	5.8	15	250
701-066	8	10.0	4.5	5.8	18	250
701-067	6	16.0	5.8	7.5	12	200
701-068	6	16.0	5.8	7.5	15	200
701-069	6	16.0	5.8	7.5	18	200
701-070	6	16.0	5.8	7.5	25	200
701-071	6	16.0	5.8	7.5	32	200
701-115	4	25.0	7.3	9.5	12	100
701-072	4	25.0	7.3	9.5	15	200
701-073	4	25.0	7.3	9.5	18	200
701-074	4	25.0	7.3	9.5	25	200
701-075	4	25.0	7.3	9.5	32	200
701-076	2	35.0	8.3	11	18	100
701-077	2	35.0	8.3	11	25	100
701-078	2	35.0	8.38	11	30	100
701-079	2	35.0	8.3	11	32	100
701-080	1/0	50.0	10.3	13	18	100
701-081	1/0	50.0	10.3	13	25	100
701-082	1/0	50.0	10.3	13	32	100

TWIN WIRE FERRULES

Part #	AWG	mm ²	color	d1	A/B	L1	L2	Bag Q'ty
701-009	2x22	0.5	Orange	1.5	4.9/2.5	15	8	500
701-116	2x22	0.5	White	1.5	4.9/2.5	15	8	500
701-089	2x20	0.75	Gray	1.8	5.2/2.6	15	8	500
701-012	2x18	0.75	White	1.8	5.2/3.2	15	8	500
701-015	2x18	1.0	Yellow	2.3	5.8/3.2	16	8	500
701-090	2x18	1.0	Red	2.3	5.8/3.2	16	8	500
701-017	2x16	1.5	Red	2.3	6.5/3.6	16	8	500
701-091	2x16	1.5	Black	2.3	6.5/3.6	16	8	500
701-120	2x16	1.5	Black	2.3	6.5/3.6	20	12	500
701-018	2x14	2.5	Blue	2.9	7.5/4.3	18	9	500
701-083	2x14	2.5	Blue	2.9	7.5/4.3	21	12	200
701-084	2x12	4.0	Gray	3.8	9.0/5.2	23	12	200
701-112	2x10	6.0	Yellow	4.9	10.7/2	26	14	100
701-114	2x6	16.0	Blue	8.4	18/9.5	30	14	50


Wire Ferrule Assortment Pack

Description	Part No.
Wire Ferrule Assortment Pack Eclipse Tools	701-998

Contents:
 50 pcs 701-011
 50 pcs 701-014
 50 pcs 701-016
 100 pcs 701-022
 100 pcs 701-028



ESD STATIC PROTECTION



www.eclipsetools.com

ESD Grounding Wrist Strap



- Elastic wrist strap
- Coil cord
- Alligator clip
- Banana Plug to alligator clip
- Band resistivity <50 Ohms

Description	Part No.
ESD Grounding Wrist Strap (Length=10 Feet)	900-002
ESD Grounding Wrist Strap (Length=6 Feet)	900-012

ESD Foot Strap



- Dual layered cup
- 1-2 Megohms resistivity

Description	Part No.
ESD Foot Strap	900-057


ESD Strap w/Hook and Loop Adjustable Strap



- Easy and quick to adjust
- Two convenient lengths to choose from
- Banana Plug to alligator clip
- Band resistivity 10⁴ Ohms

Description	Part No.
ESD Strap w/Hook and Loop Adjustable Strap (Length=10 Feet)	900-022
ESD Strap w/Hook and Loop Adjustable Strap (Length=6 Feet)	900-023

Static Protection Mat w/Ground Strap



Description	Part No.
Static Protection Mat w/Ground Strap (24"x48")	900-114
Static Protection Mat w/Ground Strap (20"x24")	900-116

ESD Wrist Strap



- Adjustable elastic strap for greater range
- Banana Plug to alligator clip
- Band resistivity 10⁴ Ohms

Description	Part No.
ESD Wrist Strap (Length=10 Feet)	900-132
ESD Wrist Strap (Length=6 Feet)	900-133

ESD Field Service Kit



- Compact & easily transported
- Folds to 8-1/2" square
- 26" x 24"
- 10 foot grounded cord ESD wrist strap

Description	Part No.
ESD Field Service Kit	900-056

Eclipse Tools




FIBER OPTICS



www.eclipsetools.com

Fiber Polishing Disks



Item #: 900-136

Item #: 902-260

- Material: Aluminum
- Channeled Base for wet polishing
- Great for wet and dry polishing

Description	Part No.
Fiber Polishing Disk 2.5mm (SC/ST/FC)	900-136
Fiber Polishing Disks 1.25mm (LC)	902-260 New

Syringe Pack



Description	Part No.
Syringe Pack (3Pc. Pack)	900-176

Foam Swabs Cleaning Kit

For clean up of organic & inorganic residue in clean room and other areas.

May be used in the following applications

- Fiber Optic Accessories
- Keyboards
- Printer carriage
- Corona wires
- Tape heads
- Ink cartridge/Chamber
- Mouse trackball
- Laser printer rollers
- Fax machine scanners
- and much more.....



Description	Part No.
Foam Swabs Cleaning Kit	900-219

Cable Splicer's Knife

- Stainless steel blade for long life
- Soft, easy to grip handle



Description	Part No.
Cable Splicer's Knife	900-135

Fiber Optic Pen Scribe



Description	Part No.
Fiber Optic Pen Scribe	900-139

Chisel Tip-Carbide Steel Fiber Scribe



- Flat, chisel geometry tip
- Carbide tip material perfect for scribing glass fiber

Description	Part No.
Chisel Tip-Carbide Steel Fiber Scribe	900-157

Eclipse Tools

Fiber Light Source - Range approx 2000 ft



- Shines light down fiber cable
- Bright light makes finding breaks easy
- To read "2.5mm SC/ST/FC"

Description	Part No.
Fiber Light Source	900-168

Fiber Viewing Scope Kit



- Inspects 2.5mm SC/ST/FC

Description	Part No.
100X Magnification Trueview brand	900-138

Fiber Optic Cable Tester

Range approx 4km

Features

- Simple, versatile, and user-friendly design
- Rugged, compact, and splash proof aluminum housing
- 650nm laser
- High output ≥ 0.5 mW
- Continuous wave output mode(CW) for steady fault illumination
- Blinking output mode increases viewing contrast
- Support 2.5 mm Connect (for PC/FC/SC/ST)
- The button switch permits easy one handed operation



New

laser class	Class 3A laser diode
Nominal wavelength	650nm/ $\pm$ 10nm
Connector interface	2.5 mm for PC/FC/SC/ST
Peak power output	≥ 0.5 mW
Operating temp.	0 ~ +40°C
Storage temp.	0 ~ +50°C
Dimensions Length	Length 160 +/- 2 mm , Diameter 13.5 mm

Description	Part No.
Fiber Optic Cable Tester	902-186N

Fiber Optic Crimping Tool

- Material: S45C DIE: AISI4140
- HRC: 45 $\pm$ 3°
- Handle: P.P.
- SC/ST/FC



Description	Application	Part No.
Fiber Optic Crimping Tool	.133", .151", .122", .188" (Hex)	902-087

Fiber Optics Tool Kit

- Crimper - with additional die for more connector types (.100"/.213"/.218"/.190" and .042/.068/.151/.178/.213)
- Nick-free strippers
- Ergonomic wire cutters
- Kevlar cutting scissors
- TrueView fiber scope kt
- SC & ST polishing disks
- Double-sided component box
- Swabs
- Alcohol bottle
- Syringe
- Tweezers
- Chisel tip scribe
- Zippered case
- SC/ST/FC



Description	Part No.
Fiber Optics Tool Kit	500-023