

長蝶番

CONTINUOUS HINGES

B-20257・B-35821～
ステンレス製・鉄製

特 徴 Feature

- 用途に応じた材質が選べます。
- 切断して使用できます。
- Suitable material can be selected according to the purpose.
- Can be cut optionally.

仕 様 ●材 質: 熱間圧延鋼板(SPHC)
冷間圧延鋼板(SPCC) (軸はステン
レス製)
ステンレス鋼板(SUS304)

●表面仕上: SPCC・SPHC/
亜鉛めっきクロメート処理(MFZn-C)

用 途 ●航空機・通信機器・測定機器・船舶・車両・小型
コンテナなどの筐体

●標準品・・・納期お問合せください

●航空機にはMS規格品をご使用ください。

●必要な寸法に切断後軸にカシメ等の抜け止め
加工をしてご使用ください。

●両端に抜け止め加工を行う場合は、必ず同じ羽
根で行ってください。異なる羽根で行うと作動
不良の原因となります。

●長尺商品のため、送料が掛かります。詳細はお
問合せください。

Speci- ●Material: Hot rolled steel plate (SPHC)
fications Cold rolled steel (SPCC)
(The axle is stainless steel)
Stainless steel (SUS304)

●Finish: SPCC, SPHC:

Zinc plating chromate treatment
(MFZn-C)

Specifi- ●Communication devices, measurement
cations devices, ships, specially equipped
vehicles, construction machinery, small
containers.

Remarks ●The MS (Military Standard) articles
must be used for the air crafts.



●The hinge is not processed to prevent
extraction of the shaft. After cutting
the hinge to size and before use, fix
stops, etc., on the shaft to prevent its
extraction.

●When fixing stops on both ends,
always fix on the same wing. Fixing
on different wings may cause faulty
operation.


B-35825-14D

B-35822-12C


商品番号 Product No.	RoHS	CAD	備考 Remarks	L ₁	L ₂	W	t	φD	製品質量(g) Mass	コード Code	単 価 Price	量販価格 数量 Quantity	Bulk Price 単価 Price
B-20257-C1	●			1829	15	19	0.8	2.0	315	11134	¥9,600	5個～	¥9,216
B-20257-C2	●			1829	15	27	1.0	3.0	570	11135	¥9,600	5個～	¥9,216
B-20257-C3	●			1829	15	32	1.2	3.0	760	11136	¥9,600	5個～	¥9,216
B-20257-C4	●			1829	15	38	1.5	3.0	1,100	11137	¥13,000	5個～	¥12,480
B-20257-C5	●	3D		1829	15	51	1.5	5.0	1,580	11138	¥13,000	5個～	¥12,480
B-20257-C6	●			1829	50	51	1.5	5.0	1,610	11139	¥13,000	5個～	¥12,480
B-35822-10C	●			1829	15	32	1.0	3.0	630	11147	¥12,000	5個～	¥11,400
B-35822-11C	●			1829	15	38	1.0	3.0	730	11148	¥12,000	5個～	¥11,400
B-35822-12C	●		SUS 304	1829	15	51	1.0	3.0	885	11149	¥12,000	5個～	¥11,400
B-35823-6C	●			1829	15	38	1.2	3.0	850	11152	¥14,000	5個～	¥13,440
B-35823-7C	●			1829	15	51	1.2	3.0	1,060	11153	¥14,000	5個～	¥13,440
B-35825-14C	●			2133	25	38	1.5	3.0	1,245	11157	¥15,000	5個～	¥14,400
B-35825-15C	●			2133	25	51	1.5	3.0	1,560	11158	¥15,000	5個～	¥14,400
B-35825-16C	●			2133	25	64	1.5	3.0	1,880	11159	¥15,000	5個～	¥14,400
B-35829-16C	●			2133	50	51	2.0	6.0	2,600	11169	¥15,000	5個～	¥14,400
B-35829-18C	●			2133	50	76	2.0	6.0	3,490	11170	¥15,000	5個～	¥14,400
B-35829-20C	●			2133	50	102	2.0	6.0	4,230	11171	¥15,000	5個～	¥14,400
B-35831-6C	●	2D		2133	50	102	3.0	10.0	7,500	11178	¥20,000	5個～	¥19,200
B-35821-8D				1829	15	27	0.8	2.0	405	11140	¥4,100	5個～	¥3,936
B-35821-10D				1829	15	38	0.8	2.0	530	11141	¥4,100	5個～	¥3,936
B-35822-9D	●			1829	15	27	1.0	3.0	615	11142	¥4,100	5個～	¥3,936
B-35822-10D	●		SPCC	1829	15	32	1.0	3.0	670	11143	¥4,200	5個～	¥3,990
B-35822-11D	●			1829	15	38	1.0	3.0	755	11144	¥4,300	5個～	¥4,085
B-35822-12D	●			1829	15	51	1.0	3.0	950	11145	¥4,400	5個～	¥4,180
B-35823-6D	●			1829	15	38	1.2	3.0	875	11150	¥6,000	5個～	¥5,760
B-35823-7D				1829	15	51	1.2	3.0	1,115	11151	¥6,000	5個～	¥5,760
B-35825-14D				2133	25	38	1.6	3.0	1,435	11154	¥6,000	5個～	¥5,700
B-35825-15D				2133	25	51	1.6	3.0	1,680	11155	¥6,000	5個～	¥5,700
B-35825-16D				2133	25	64	1.6	3.0	2,035	11156	¥6,000	5個～	¥5,700
B-35826-10D				2133	25	38	1.6	5.0	1,630	11160	¥6,000	5個～	¥5,700
B-35826-11D				2133	25	51	1.6	5.0	1,960	11161	¥6,000	5個～	¥5,700
B-35826-12D				2133	25	64	1.6	5.0	2,345	11162	¥6,000	5個～	¥5,700
B-35829-11D				2133	50	51	2.0	5.0	2,500	11163	¥6,000	5個～	¥5,700
B-35829-13D				2133	50	76	2.0	5.0	3,310	11164	¥6,000	5個～	¥5,700
B-35829-15D			SPHC	2133	50	102	2.0	5.0	4,185	11165	¥6,200	5個～	¥5,890
B-35829-16D				2133	50	51	2.0	6.0	2,690	11166	¥6,200	5個～	¥5,890
B-35829-18D				2133	50	76	2.0	6.0	3,520	11167	¥6,200	5個～	¥5,890
B-35829-20D				2133	50	102	2.0	6.0	4,300	11168	¥6,200	5個～	¥5,890
B-35830-11D				2133	50	76	2.3	6.0	4,030	11172	¥9,000	5個～	¥8,640
B-35830-13D				2133	50	102	2.3	6.0	4,870	11173	¥9,000	5個～	¥8,640
B-35830-14D				2133	50	127	2.3	6.0	5,870	11174	¥10,000	5個～	¥9,500
B-35831-6D				2133	50	102	3.2	10.0	7,980	11175	¥10,000	5個～	¥9,500
B-35831-7D				2133	50	127	3.2	10.0	9,205	11176	¥11,000	5個～	¥10,450
B-35831-8D				2133	50	153	3.2	10.0	10,800	11177	¥12,000	5個～	¥11,400

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。



軸はステンレス製です。Shaft is made of stainless steel

CONTINUOUS HINGES
長蝶番
平蝶番
裏蝶番
抜き差し
蝶番
段付
蝶番
クリーン
ヒンジ
特装車
蝶番
フリーザー
ヒンジ
特殊
蝶番
トルク
ヒンジ
ステー
周辺機器
(B)