


## Desk-top cases – *comptec*

19" case, 6 U, 7 U, 9U




02202002




CTTP0002

Front view



h = case foot height, HE = U, internal usable height

Side view



Usable depth d = D - 24 mm

CTA42312

- Desk-top case (pre-fitted)
- With handle shell
- Top cover, base plate and rear panel in steel
- Front and rear frames in die-cast Al
- Ventilation slits in rear panel and base

### Delivery comprises (kit)

| Item | Qty | Description                                                               |
|------|-----|---------------------------------------------------------------------------|
| 1    | 1   | Front frame, Al die-cast, RAL 7016, with 19" grid                         |
| 2    | 1   | Rear frame, Al die-cast, RAL 7016, with 19" grid                          |
| 3    | 2   | Side profile at top, Al extrusion, RAL 7016                               |
| 4    | 2   | Side profile at bottom, Al extrusion, RAL 7016                            |
| 5    | 2   | Side panel, St, 1.5 mm, RAL 9006, with GND/earthing tag                   |
| 6    | 2   | Handle shell, PC, RAL 7016, UL 94 V-0, load-carrying capacity: 60 kg/pair |
| 7    | 1   | Cover plate, St, 1 mm, RAL 9006, with GND/earthing tag                    |
| 8    | 1   | Base plate, St, 1 mm, RAL 9006, with GND/earthing tag                     |
| 9    | 1   | Rear panel, St, 1 mm, RAL 9006, with GND/earthing tag                     |
| 10   | 4   | Case foot with anti-slip protection, PC, black, UL 94 V-0                 |
| 11   | 1   | Assembly kit                                                              |

Items 1, 2, 3, 4, 5, 6 and 9 fitted.

### Order Information

|   | Height H | h  | Depth D | Usable depth d | Width B | Part no.  |
|---|----------|----|---------|----------------|---------|-----------|
| U | mm       | mm | mm      | mm             | mm      |           |
| 6 | 286      | 13 | 300     | 276            | 520     | 10225-604 |
| 6 | 286      | 13 | 400     | 376            | 520     | 10225-615 |
| 6 | 286      | 13 | 500     | 476            | 520     | 10225-626 |
| 6 | 286      | 13 | 600     | 576            | 520     | 10225-637 |
| 7 | 331      | 13 | 400     | 376            | 520     | 10225-616 |
| 7 | 331      | 13 | 500     | 476            | 520     | 10225-627 |
| 7 | 331      | 13 | 600     | 576            | 520     | 10225-638 |
| 9 | 420      | 13 | 400     | 376            | 520     | 10225-618 |
| 9 | 420      | 13 | 500     | 476            | 520     | 10225-629 |
| 9 | 420      | 13 | 600     | 576            | 520     | 10225-640 |

### Note

- Please order GND/earthing kit separately, see page 5.106
- The case foot, item 10, can be replaced by a tip-up foot, see page 5.107
- Please order slide rails separately, see page 5.105
- Handle shell, item 6, can be replaced by a folding handle, see page 5.105



For further information [www.schroff.biz/oneclick](http://www.schroff.biz/oneclick)  
oneClick search code = Part no.



ServicePLUS see page 5.4