


Dimensions: mm (In)

**Electrical Specifications:**

- Rating: 5A 120VAC/28VDC, 2A/250VAC
- Contact resistance: 10mΩ max. @ 2~4VDC 100mA
- Insulation resistance: 1,000MΩ min.
- Dielectric strength: 1000Vrms @ epoxy seal level
- Electrical life: 50,000 make-and-break cycles

Mechanical Specifications:

- Circuit: 3P SPDT (On)-Off-(On)
- Operating temperature: -30°~+85°C

Materials:

- Case: dialyl phthalate
- Handle: chrome plated brass
- Bushing: nickel plated brass
- Housing: stainless steel
- Terminal/switch support: electrotin plated brass
- Contacts: silver plated copper

Toggle Switch
103-5145

Mountain
Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-5145](#)