




④规格 Specifications

额定负荷 Ratings	DC 30 V 0.3 A
初期接触电阻 Initial Contact Resistance	30 mΩ Max.
绝缘电阻 Insulation Resistance	DC500 V 60 Sec.100 MΩ Min.
抗电强度 Dielectric	AC 500 V(50~60HZ) 60 Sec.

操作力 Operating Force (gf)	 
	200±100 300±150
負荷寿命 Operating Life With Load	10,000 次 Cycles

6	弹片 SPRING PLATE	SUS	1	NATURAL
5	端子 TERMINAL	C2680R①	10	Ag PLATED
4	基板 TERMINAL BASE	PHENOL RESIN	1	YELLOW
3	接触片 CONTACT	C5210R②	2	Ag CLAD
2	胶柄 KNOB	P O M	1	G 2 - 12
1	铁壳 FRAME	S P C C	1	Sn PLATED
序NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS

A01	ADD: 规格 Specifications 见 ①	王光云	06-04-26
	C2680R-EH → C2680R 见 ①		
	C5210R-EH/Ag CLAD → C5210R 见 ①		
01		赖立辉	4 MAY 96
标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE
DWG NO. <u>ITEM0576</u>			

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE	SLIDE SWITCH		ITEM NO	SS-23D28-G		
UNDER 1	± 0.10	DRAWN	王光云	06-04-26	VERSION	A01	PAGE 1	OF 1
1 - 10	± 0.30	REVIEWED	张念明	06-04-26	SCALE		UNIT	mm
OVER 10	± 0.50	APPROVED	林高全	06-04-26	PROJECTION			

COMAX ELECTRONICS (HUIZHOU) CO.,LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Components:

[SS-23D28-G 5 NS](#)