

5.0V, HCMOS, SMD Oscillator



Model: F3345 SERIES

RoHS Compliant / Pb Free

Rev. 1/29/2014

Page 1 of 2

http://www.foxonline.com/need_a_sample.htm

Need a
Sample®

FEATURES

- 5.0V Operation
- HCMOS/TTL Output
- Tri-State Enable/Disable
- Tape and Reel (2,000 pcs. STD)

OPTIONS

- Standby Function (F4101)

• PART NUMBER SELECTION

Part Number	Model Number	Frequency Stability ¹	Operating Temperature (°C)	Frequency Range (MHz)
092-Frequency-xxxxx	F3345	±100PPM	-10 ~ +70	1.000 ~ 80.000
093-Frequency-xxxxx	F3345R	±100PPM	-40 ~ +85	1.000 ~ 80.000
090-Frequency-xxxxx	F3340	±50PPM	-10 ~ +70	1.000 ~ 80.000
091-Frequency-xxxxx	F3340R	±50PPM	-40 ~ +85	1.000 ~ 80.000
094-Frequency-xxxxx	F3346	±25PPM	-10 ~ +70	1.000 ~ 80.000
095-Frequency-xxxxx	F3346R	±25PPM*	-40 ~ +85	1.000 ~ 80.000
096-Frequency-xxxxx	F3348	±20PPM*	-10 ~ +70	1.000 ~ 80.000

• ELECTRICAL CHARACTERISTICS

PARAMETERS	MAX (unless otherwise noted)
Frequency Range (Fo)	1.000 ~ 80.000 MHz
Storage Temperature Range (T _{STG})	-55°C ~ +125°C
Supply Voltage (V _{DD})	5.0V ± 10%
Input Current (I _{DD})	
1.000 ~ 25.000 MHz	25mA
25.000+ ~ 50.000 MHz	40mA
50.000+ ~ 67.000 MHz	60mA
67.000+ ~ 80.000 MHz	73mA
Output Symmetry (50% V _{DD})	45% ~ 55%
Rise Time (10% ~ 90% V _{DD}) (T _R)	7nS
Fall Time (90% ~ 10% V _{DD}) (T _F)	7nS
Output Voltage (V _{OL})	10% V _{DD}
(V _{OH})	90% V _{DD} Min
Output Current (I _{OL})	16mA Min
(I _{OH})	-16mA Min
Output Load	
TTL	10TTL
HCMOS	50pF
Start-up Time (T _s)	10mS
Enable/Disable Time ²	100nS
Maximum Soldering Temp / Time	260°C / 10 Seconds
Moisture Sensitivity Level (MSL)	1
Termination Finish	Au


¹ Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, aging, shock, and vibration. *Excludes Shock/Vibration

² An internal pullup resistor from pin 1 to pin 4 allows active output if pin 1 is left open.

Note: A 0.01µF bypass capacitor should be placed between VDD (Pin 4) and GND (Pin 2) to minimize power supply line noise.

Drawing is for reference to critical specifications defined by size measurements.

Certain non-critical visual attributes, such as side castellations, reference pin shape, etc. may vary. All specifications subject to change without notice.



• ENABLE / DISABLE FUNCTION

INH (Pin 1)	OUTPUT (Pin 3)
OPEN ²	ACTIVE
'1' Level V _{IH} ≥ 70% V _{DD}	ACTIVE
'0' Level V _{IL} ≤ 30% V _{DD}	High Z

5.0V, HCMOS, SMD Oscillator



Model: F3345 SERIES

RoHS Compliant / Pb Free

Rev. 1/29/2014

Page 2 of 2

http://www.foxonline.com/need_a_sample.htm

Need a
Sample®

• TAPE SPECIFICATIONS (millimeters)							
MODEL	A	B	C	D	E	F	STD Reel QTY
F3345 Series	Ø1.5	4.0	8.0	7.5	16.0	2.15	2,000

• REEL SPECIFICATIONS (millimeters)							
MODEL	G	H	I	J	K	L	M
F3345 Series	2.0	Ø13	Ø21	Ø80	Ø255	17.5	2.0

