




JKL PART NO.: CF20305-24B

JKL LAMP PART NO.	COLOR WHITE	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS) (AVG.)
CF20305-24B	x = 0.278±0.01 y = 0.264±0.01	1750 @ 0°C	780	5	42,000 TYP.	40,000

* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0	JKL COMPONENTS CORPORATION							
					TITLE MINIATURE COLD CATHODE FLUORESCENT LAMP							
			DRAWN BY	APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.				
A			START VOLTS TO 2600 & OPER. VOLT TO 1400	8/23/07	L. WENGSTROM	L.R.	8/28/07	A	55335	CF20305-24B		
			RELEASED	11/10/05								
REV. NO.	DESCRIPTION/ECO NUMBER			APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET
								NONE	11/10/05	8/28/07	A	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[CF20305-24B](#)