






NOTES:

1. Dimensions are in inches & [mm].
2. Socket body: Glass-filled polyester, 94 VO rating, green in color
3. Receptacle shell: 360 brass, with 200 μ in tin over 100 μ in nickel
4. Receptacle contacts: Beryllium copper with 30 μ in gold over 50 μ in nickel
5. The continuous temperature rating of the socket shall be 150° C.
6. Contact resistance: 20 milliohms or less.



DETAIL A
SCALE 2:1



TOLERANCES - UNLESS OTHERWISE SPECIFIED

.XX = ±.01 [.254]
 .XXX = ±.005 [.127]
 ANG. = ±5°



TITLE:

TO-3 SOCKET

SUBJECT:

MECHANICAL DRAWING

ENGINEER:

D-M

R.MOR

DCAL

13241

SHL

1

OF

1

MODEL:

MS03

FILENAME:

MS03

REV:

G

DATE:

03JUN13