


| ITEM NO. | PART NUMBER | DESCRIPTION                                               | QTY. | NOTES          |
|----------|-------------|-----------------------------------------------------------|------|----------------|
| 1        | TLY-13      | NEMA 5-15P                                                | 1    | black overmold |
| 2        | TLY-18      | C13                                                       | 1    | black overmold |
| 3        | 30-00248    | Wire, 3C, 18 AWG, UL SJT, 300V, 105°C, 7.75 mm, VW-1, PVC | 1    |                |



|          |            |                 |                                                                                                                                                                                     |                                                                                           |                                                                                                                                                                       |             |         |              |
|----------|------------|-----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|---------|--------------|
| Revision | Date       | Description     | Notes<br><br>Rated for 10 A at 125 Vac<br><br>RoHS, REACH and Dodd-Frank conflict materials compliant<br><br>Function test: no open, no reversed polarity, no short circuit, no INT |                                                                                           | <div>TENSILITY</div><br><div>20802 Sockeye Place #130<br/>Bend, OR 97701 USA<br/>tel 541.323.3228    fax 541.323.4202<br/>800 877.670.7118    www.tensility.com</div> |             |         |              |
| A        | 12/19/2012 | Initial release |                                                                                                                                                                                     |                                                                                           |                                                                                                                                                                       |             |         |              |
|          |            |                 |                                                                                                                                                                                     |                                                                                           |                                                                                                                                                                       |             |         |              |
|          |            |                 |                                                                                                                                                                                     |                                                                                           |                                                                                                                                                                       |             |         |              |
|          |            |                 | DIMENSIONS ARE IN MILLIMETERS                                                                                                                                                       | DESCRIPTION:                                                                              | SIZE                                                                                                                                                                  | Part number |         |              |
|          |            |                 | TOLERANCES:<br>X:    ± 0.5 mm<br>X.X: ± 0.3 mm<br>X.XX: ± 0.05 mm                                                                                                                   | Ac cord, 1000 mm, U.S, NEMA 5-15P plug, TLY-13 to C13, TLY-18, 18 AWG, SJT wire, 30-00248 | A                                                                                                                                                                     | 11-00024    |         |              |
|          |            |                 |                                                                                                                                                                                     |                                                                                           | SCALE:1:2                                                                                                                                                             |             | WEIGHT: | SHEET 1 OF 1 |