


NOTES

- 1 FOR MINI-APPLICATOR CRIMPING
- 2 UNDERCOATING 1,25 μ M Ni, SELECTIVE 0,8 μ M Au, NO GOLD FLASH
- 3 UNDERCOATING 1,25 μ M Ni, SELECTIVE 0,8 μ M Au, REMAINDER GOLD-FLASH
- 4 ZONE I BRIGHT TIN/LEAD PLATED
- 5 PRE TIN PLATED 2,0 μ M
- 6 MATERIAL: PHOS BRONZE



CUSTOMER COPY FOR REFERENCE ONLY

©1982 BY AMP HOLLAND N.V. ALL RIGHTS RESERVED A.M.P. PRODUCTS COVERED BY PATENTS AND OR PATENTS PENDING



AMP HOLLAND B.V.
s Hertogenbosch

167022 -3	167025 3	TIN	5
167022 -2	167025 2	GOLD	3
167022 1	167025 -1	GOLD	4/2

WIRE RANGE 28-38 AWG 0.03-0.09mm	NSU RANGE 0.020-0.040 0.5-1.02mm	RS USED
--	--	---------

ORDER NO	LOOSE PIECE	PLATING
----------	-------------	---------

SCALE 8:1	SIZE A	NO C-167022 -E	REV 0
--------------	-----------	-------------------	----------

DR L. Jans 7/5 82	DE	DA E
CHK C. Jans 11/5 82	DATE	APP 11/5 82

NAME AMP MODU MOD V RECEPTACLE