



Sample photo

Order symbol: CAB PC 403018 G3B
Product nbr: 8113352
Description: Cabinet, PC
Remarks: Locks on the long side

EAN: 6418074020246
El. number:
 Finland 3424118
 Denmark 8212019247
 Italy 7821045
 Sweden 2539975

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:			Rating:			
	L	W	H			
mm:	400	300	180	Ingress Protection (EN 60529): IP 65		
inch:	15.7	11.8	7.1	Impact Resistance (EN 50102): IK 08		
Materials:				Electrical insulation: Totally insulated		
Material:	PC			Halogen free (DIN/VDE 0472, Part 815): Yes		
Base colour:	RAL 7035			UV resistance: UL 508		
Cover colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 5V		
Gasket material:	EPDM			Glow Wire Test (IEC 695-2-1) °C: 960		
Temperatures:				UL Type: UL TYPE 1, 4, 4X, 12, 13		
Short term:	-40 ... 120 °C			Certificates:		
Continuous:	-40 ... 80 °C			Germanischer Lloyd (GL)		
Short term:	-40 ... 250 °F			Underwriters Laboratories		
Continuous:	-40 ... 175 °F			Fimko		
Accessories:				Lloyds Register of Shipping (LR)		
EKIV 43	Mounting plate			Europe EN 50298 1998		
EKIV 27	DIN-35 Mounting rail			UL Canada		
EKIV 37	DIN-35 Mounting rail			Gost R		
FP A 43	Swing-out door, aluminium					
FP 43	Front plate					
FP 12x2-43	Front Plate					
FP 12x3-43	Front Plate					
DRF 43/44	DIN rail frame set					

