


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECR-16-007103	25JUN2016	GSK	AP


- Notes:
- Assembly per assembly instruction 114-32111.
 - Electrical test:
100% open short & miss wire test
contact resistance: 2 Ohm max
 - Stripped and tinned. Maximum conductor diameter after tinning 2.10mm.
 - Nut does not need to be completely screwed.



WIRING SCHEME	
CONNECTOR HOUSING (ITEM 1)	WIRE
PE/	GREEN/YELLOW
N	BLUE
L	BROWN

2829470-1
TE P/N

0.41	M	WIRE, HOOKUP, H05V-K, 1.5mm, (YELLOW/GREEN)	8
0.41	M	WIRE, HOOKUP, H05V-K, 1.5mm, (BLUE)	7
0.41	M	WIRE, HOOKUP, H05V-K, 1.5mm, (BROWN)	6
1	PC	PANEL SEAL NECTOR M-LINE	5
1	PC	3P SCREW NUT, PNL MNT	4
1	PC	LOCKING FOR CONTACTS M-LINE, -2	3
3	PC	PIN, CRIMP, 16-18 AWG	2
1	PC	3P PIN HSG, PNL MNT, CODE A	1
QTY	UoM	DESCRIPTION	ITEM



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.BURZYŃSKI 25MAY2015	TE Connectivity		
DIMENSIONS: mm		CHK A.V.ZANDVOORT 25MAY2015			
		APVD A.V.ZANDVOORT 25MAY2015	NAME PIGTAIL BULKHEAD PIN STD HARMONIZED CABLE		
		PRODUCT SPEC	—		
MATERIAL —		APPLICATION SPEC	—		
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-2829470
FINISH —		CUSTOMER DRAWING			RESTRICTED TO —
		SCALE NTS	SHEET 1 OF 1	REV D	