



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

NTE1337

Integrated Circuit

Module – Hybrid, Audio Power Amp

70 Watt, 2 Power Supplies Required

Features:

- Minimum Output Power – 70W
- Dual Power Supply – Single Channel
- Thick Film Hybrid
- Load Shorting Protector

Absolute Maximum Ratings:

Supply Voltage, V_{CC} $\pm 55V$
 Collector Current, I_C 7A
 Operating Case Temperature, T_C $+85^{\circ}C$
 Storage Temperature Range, T_{stg} -30° to $+100^{\circ}C$
 Thermal Resistance, Junction to Case, $R_{\theta JC}$ $1.4^{\circ}C/W$

Electrical Characteristics: ($T_A = +25^{\circ}C$, $V_{CC} = \pm 42V$, $R_L = 8\Omega$, $R_g = 600\Omega$, $V_G = 26.4dB$)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Quiescent Current	I_{CCO}	$V_{CC} = \pm 50V$	–	50	100	mA
Output Power	$P_{O(1)}$	THD = 0.2%, $f = 20$ to $20kHz$	70	–	–	W
	$P_{O(2)}$	THD = 0.2%, $f = 1kHz$	–	80	–	W
	$P_{O(3)}$	THD = 0.2%, $V_{CC} = \pm 50V$, $f = 1kHz$	–	100	–	W
Total Harmonic Distortion	THD ₍₁₎	$P_O = 1$ to $70W$, $f = 20$ to $20Hz$	–	–	0.2	%
	THD ₍₂₎	$P_O = 1W$, $f = 1kHz$	–	0.03	–	%
Frequency Response	f	$P_O = 1W$, $+0dB$, $-1dB$	10 to 100k			Hz
Input Resistance	r_i	$P_O = 1W$, $f = 1kHz$	–	52	–	$k\Omega$
Output Noise Voltage	V_{NO}	$V_{CC} = \pm 50V$, $R_g = 10k\Omega$	–	0.3	0.5	mV_{rms}
Noise Voltage	V_N	$V_{CC} = \pm 50V$, -70	-70	–	70	mV

Pin Connection Diagram

