


Item		Unit	Specification
AWG		AWG	24AWG(0.22mm ²)
No. of conductor		P.C	2F
Conductor	Material	-----	Bared Copper Wire
	Filler	-----	-----
	Construction	No./mm	7/0.2mm
	Stranded diameter	mm	0.6112mm
Insulation	Material	----	PVC
	Nom. Thickness	mm	0.6mm
	Diameter	mm	1.8*3.6mm
	Color	----	----
Electric Characters	Rated temperature	°C	80°C
	Rated voltage	V	300V
	Conductor Resistance at 20°C	Ohm/kft	31
	Withstand voltage spark	kv/sec	3KV
Jacket	Material		-----
	Nom. Thickness	mm	-----
	O.D	mm	-----
	Color	----	-----
Marking	xxxxxx		

Configuration:



GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO. 100280		GOLDSUN NO.	
Description SPEAKER POWER CABLE 24AWG 2 CONDUCTOR STRANDED			Rev. 1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: