



Direct Mount Terminals

Feed Through


EKS 12/4



MK 3




MK 3




Technical Data			UL	CSA	VDE	UL	CSA	VDE
Rated voltage			300 V	300 V	500 V	300 V	300 V	
Rated current			20 A	20 A	24 A	20 A	25 A	
Wire size	AWG		#22...12	#22...12	2.5 mm ²	#22...12	#22...12	
Insulation stripping length	mm (in.)		5 (.20)			5 (.20)		
Torque	Nm (lb. in.)		.9 (8.0)			.9 (8.0)		
Number of poles			12			12		
Molding material			Polyamide (white)			Melamine		
Terminal Strips			Type	Length mm (in.)	Part No.	Type	Length mm (in.)	Part No.
12 pole			EKS 12/4	126 (4.96)	62350	MK 3/12	109.9 (4.33)	24352
Cutoffs								
2 pole			EKS 2/4	20.2 (.795)	62450	MK 3/2	17.95 (.707)	27382
3 pole			EKS 3/4	30.9 (1.22)	62440	MK 3/3	27.20 (1.07)	27392
4 pole			EKS 4/4	41.6 (1.64)	62430	MK 3/4	36.45 (1.44)	27402
5 pole			EKS 5/4	52.3 (2.06)	62420	MK 3/5	45.70 (1.80)	27412
6 pole			EKS 6/4	63.0 (2.48)	62410	MK 3/6	54.95 (2.16)	27422
7 pole			EKS 7/4	73.7 (2.90)	62400	MK 3/7	64.20 (2.53)	27432
8 pole			EKS 8/4	84.4 (3.32)	62390	MK 3/8	73.45 (2.89)	27442
9 pole			EKS 9/4	95.1 (3.74)	62380	MK 3/9	82.70 (3.26)	27452
10 pole			EKS 10/4	105.8 (4.17)	62370	MK 3/10	91.95 (3.62)	27462
11 pole			EKS 11/4	116.5 (4.59)	62360	MK 3/11	101.2 (3.98)	27472


MK 6



MK 6



MK 10*



Technical Data			UL	CSA	VDE	UL	CSA	VDE
Rated voltage			300 V	300 V	690 V	300 V	300 V	690 V
Rated current			30 A	40 A	41 A	30 A	40 A	41 A
Wire size	AWG		#22...10	#22...12	6 mm ²	#22...12	#22...10	6 mm ²
Insulation stripping length	mm (in.)		9 (.35)			9 (.35)		
Torque	Nm (lb. in.)		2.3 (20)			2.3 (20)		
Number of poles			6			6		
Molding material			Melamine			Polyamide		
Terminal Strips			Type	Length mm (in.)	Part No.	Type	Length mm (in.)	Part No.
MK 6/6			MK 6/6	75 (2.95)	62012	MK 6/6	74.90 (2.95)	62016
Cutoffs								
2 pole			MK 6/2	24.45 (.963)	62042	MK 6/2	24.45 (.963)	62046
3 pole			MK 6/3	37.45 (1.47)	62032	MK 6/3	37.45 (1.47)	62036
4 pole			MK 6/4	50.45 (1.99)	62022	MK 6/4	50.45 (1.99)	62026
5 pole								
6 pole			MK 6/6	75 (2.95)	62012	MK 6/6	74.90 (2.95)	62016
7 pole								
8 pole								
9 pole								
10 pole								
11 pole								
12 pole								
			BSTb	17/6	30460	BSTb	17/6	30460

*Can be mounted using glue or with M3 x 12 screws through the terminal screw hole. Cutoff versions provide mounting holes.

PART NUMBER SELECTION TABLES

Weidmüller