

WB20

Low profile quad band GSM Antenna

Features

- ◆ Groundplane Independent
- ◆ Covers 850/900/1800/1900 MHz bands
- ◆ Cable exit from bottom
- ◆ Gasket forms weatherproof seal

Specifications

Specifications	
Radiating element	1/2 Wave Element
Frequency range	850/900/1800/1900 MHz
Peak gain	0 dBi
Polarisation	Linear
Return loss	-9.0 dB
Power rating	10W
Cable / Connector	2M RG-174 and SMA-Male
Dimensions	80 x 23mm (d x h)

Popular Ordering Options


FWB235164-SM-2K	WB20 with 2M RG-174 and SMA-Male Connector
FWB235164-FM-2K	WB20 with 2M RG-174 and FME-Female Connector

Specifications subject to change without notice.




WB20 | Low Profile GSM Antenna

Return Loss



Outline Drawing



Specifications subject to change without notice.

5 Little Balmer
Buckingham Industrial Park
Buckingham
MK18 1TF
UK

Tel: +44 (0)1280 824055
Fax: +44 (0)1280 817179
Email: sales@ead-ltd.com
Web: www.ead-ltd.com