



### FEATURES:

- Simplified attachment of cables or small components by means of set screws.
- For test versatility, banana plugs can be vertically stacked to the banana plug.
- Banana plug spring is Beryllium Copper for long insertion life.
- Model 4898 features Polyphenylene Sulfide for high temperature operation.
- Model 4892 features gold plating for superior electrical connection.

### MATERIALS:

Banana Plug: Body - Brass, Nickel Plated (Model 4892, Gold Plated)

Spring: Beryllium Copper, Nickel Plated, (Model 4892 , Gold Plated)

Insulation: ABS Molded ( Model 4898 Polyphenylene Sulfide), Color: Per Part Number

Marking: "Model Number" and "POMONA ELECTRONICS CO, INC. POMONA, CALIFORNIA"

Set Screws (#8-32 Single Slot): Steel, Zinc Plated

### RATINGS:

Voltage: Hand-held Testing: 30VAC/60VDC Max.

Hand Free Testing in controlled Voltage Environment: 5000 WVDC.

Current: 15 Amperes

Operating Temperature: +50°C (+122°F) Max., Model 4898 +150°C (+302°F)

### ORDERING INFORMATION: Model #- Color Code

MDP Std. Colors: -0 Black., -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

4892 Std. Colors: -0 Black, -2 Red

4898 Std. Colors: -0 Black, -6 Blue.

Ordering Example: 4892-2 Gold Plated Double Banana Plug, Color: Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4892-0](#) [4892-2](#) [4898-0](#) [4898-6](#)