

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [49517-1300](#)
Status: **Active**
Description: 3.96mm Pitch Wire-to-Board Female Housing, 13 Circuits, Natural

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-49517-001 \(PDF\)](#)
[Packaging Specification PK-49517-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E29179


General
Product Family Crimp Housings
Series [49517](#)
Application Power, Wire-to-Board
Product Name N/A
UPC 822350246392

Physical
Breakaway No
Circuits (maximum) 13
Color - Resin Natural
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 2.466/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.96mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -25°C to +85°C

Electrical
Current - Maximum per Contact 7A

Material Info

Reference - Drawing Numbers
Packaging Specification PK-49517-001
Product Specification PS-49517-001
Sales Drawing SD-49517-001



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[49517Series](#)

Mates With
[35978](#) Header

Use With
[359229002](#) Wire-to-Board Terminal. [49518](#) TPA™

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

49517-1300