



Type: CDR105
◆ Product Description

- 10.4×9.6mm Max.(L×W), 5.5mm Max. Height
- Inductance range: 10~470 μ H.
- Rated current range: 0.37~2.53A.
- In addition to the standards versions shown here, custom inductors are also available to meet your exact requirements.


◆ Feature

- Magnetically shielded construction.
- Storage temperature range: -40°C~+100°C.
- Operating temperature range: -40°C~+100°C (Including coil's self temperature rise).
- Ideally used in Notebook PC ,LCD TV ,Game machine ,HDD,DSC/DVC, etc as DC-DC converter inductors.
- RoHS compliance and Halogen free.

◆ Dimensions (mm)

◆ Land Pattern (mm)


Type: CDR105
◆ Specification

Part name ※	Stamp	Inductance (μ H) ※ 1	D.C.R.(Ω) Max (at 20°C)	Rated Current (A) ※2	S.R.F (MHZ) [typ.]
CDR105NP-100M□	100M	+20% 10—15%	0.06	2.53	31
CDR105NP-120M□	120M	+20% 12—15%	0.06	2.31	27
CDR105NP-150M□	150M	+20% 15—15%	0.07	2.06	27
CDR105NP-180M□	180M	+20% 18—15%	0.08	1.89	26
CDR105NP-220M□	220M	+20% 22—15%	0.09	1.71	21
CDR105NP-270M□	270M	+20% 27—15%	0.11	1.54	18
CDR105NP-330M□	330M	+20% 33—15%	0.12	1.39	16
CDR105NP-390M□	390M	+20% 39—15%	0.16	1.28	15
CDR105NP-470M□	470M	+20% 47—15%	0.18	1.17	14
CDR105NP-560M□	560M	+20% 56—15%	0.19	1.07	12
CDR105NP-680M□	680M	+20% 68—15%	0.22	0.97	11
CDR105NP-820M□	820M	+20% 82—15%	0.28	0.88	10
CDR105NP-101M□	101M	+20% 100—15%	0.35	0.80	7.0
CDR105NP-121M□	121M	+20% 120—15%	0.38	0.73	6.5
CDR105NP-151M□	151M	+20% 150—15%	0.45	0.65	5.8
CDR105NP-181M□	181M	+20% 180—15%	0.62	0.60	5.3
CDR105NP-221M□	221M	+20% 220—15%	0.69	0.54	5.2
CDR105NP-271M□	271M	+20% 270—15%	0.78	0.49	4.6
CDR105NP-331M□	331M	+20% 330—15%	1.03	0.44	4.2
CDR105NP-391M□	391M	+20% 390—15%	1.18	0.41	3.6
CDR105NP-471M□	471M	+20% 470—15%	1.60	0.37	3.6

Type: CDR105**※ Description of part name**

CDR105NP-100M□

└─	B	Box
└─	C	Carrier Tape

※1: Measuring frequency: $10\ \mu\text{H} \sim 82\ \mu\text{H}$ at 2.52 MHz; $100\ \mu\text{H} \sim 470\ \mu\text{H}$ at 1 kHz.※2: Rated current: The D.C. current at which the inductance decreases to 80% of it's nominal value or when $\Delta t=40^{\circ}\text{C}$, whichever is lower($T_a=20^{\circ}\text{C}$).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sumida:

[CDR105NP-820NC](#) [CDR105NP-271NC](#) [CDR105NP-181NC](#) [CDR105NP-331NC](#) [CDR105NP-270NC](#) [CDR105NP-121NC](#) [CDR105NP-100NC](#) [CDR105NP-180NC](#) [CDR105NP-391NC](#) [CDR105NP-221NC](#) [CDR105NP-101NC](#) [CDR105NP-330NC](#) [CDR105NP-470NC](#) [CDR105NP-150NC](#) [CDR105NP-560NC](#) [CDR105NP-120NC](#) [CDR105NP-680NC](#) [CDR105NP-390NC](#) [CDR105NP-471NC](#) [CDR105NP-151NC](#) [CDR105NP-220NC](#)