

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0851062139
Status: Obsolete
Description: 2.50mm (.098") Pitch Omnigrid Receptacle, Right Angle, 9SU, 167 Circuits

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Backplane Connectors
Series	85106
Application	Daughtercard
Comments	Performance Level 1 Lubricated
Component Type	PCB Receptacle
Product Name	Omnigrid
Style	N/A

Physical

Circuits (Loaded)	167
Circuits (maximum)	425
Color - Resin	Gray
Durability (mating cycles max)	500
Keying to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Material - Resin	Polycarbonate
Number of Columns	N/A
Number of Pairs	N/A
Number of Rows	5
Orientation	Right Angle
PCB Retention	None
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Pitch - Mating Interface	2.50mm (.098")
Plating min - Mating	2.032µm (80µ")
Plating min - Termination	0.203µm (8µ")
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Through Hole - Compliant Pin


Electrical

Current - Maximum per Contact	1A
Data Rate	N/A
Voltage - Maximum	750V

Material Info

Reference - Drawing Numbers

Product Specification	PS-851**-0005
Sales Drawing	SDA-85106-0***, SDA-85106-2139



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[85106Series](#)