

Products ▶ Systems ▶ Mid-Tower ▶ [7037A-i]



Black

► Drivers & Utilities ► BIOS ► Tested Memory / HDD

1. Intel® Xeon® processor E5-2600 family; QPI up to 8GT/s
2. Up to 512GB DDR3 1600MHz ECC Registered DIMM; 16x DIMM sockets
3. Expansion slots: 3 (x16) PCI-E 3.0, 2 (x8) PCI-E 3.0 & 1 (x4) PCI-E 3.0
4. Intel® i350 Dual port Gigabit Ethernet
5. 2x SATA3 and 8x SATA2 ports
6. 4x 3.5" SAS/SATA HDD bays, 90° rotating hard drive cage, 4x 2.5" internal HDD/SSD bays (opt.)
7. 900W High Efficiency Power Supply

80PLUS, Gold Level Certified

Note: Image above may show a varied configuration or optional parts. Please refer to parts list for standard parts included.

Specifications

BIOS Type	■ 64Mb SPI Flash EEPROM with AMI® BIOS
BIOS Features	■ Plug and Play (PnP) ■ APM 1.2 ■ DMI 2.3 ■ ACPI 1.0 / 2.0 ■ USB Keyboard support ■ SMBIOS 2.3 ■ UEFI

RoHS	RoHS Compliant
Environmental Spec.	- Operating Temperature: 10°C to 35°C (50°F to 95°F) - Non-operating Temperature: -40°C to 70°C (-40°F to 158°F) - Operating Relative Humidity: 8% to 90% (non-condensing) - Non-operating Relative Humidity: 5% to 95% (non-condensing)

[See Parts List](#)