



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor
- Install & Maintain
- Installation Instructions
 - PDFPan-Shrink H ..

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'HSTTRA12-48-Q'

Your search criteria matched only one product, shown below

HSTTRA12-48-Q



- Dual Wall Polyolefin DAMP-SHRINK™Heat Shrink Tubing in 4 ft (1.2M) Pieces
- For damp locations
 - Semi-rigid tubing
 - Adhesive inner wall seals and protects components from moisture and corrosion

- Provides a rugged seal against the elements
- Material Type: Polyolefin Cross -Linked with adhesive
- Ratio: 2.5:1
- Temperature Range: -67°F to 230°F (-55°C to 110°C)
- Voltage Rating: 600V
- Mil Spec: AMSDTL-23053/4 Class 1

Part Number	HSTTRA1248-Q
RoHS Compliancy Status	Compliant
Part Description	Dual Wall Adhesive Lined SemRigid Heat Shrink
Material	Polyolefin cross-linked with adhesive.
Color	Black
Military Specification	AMS-DTL-23053/4 Class 1
Length (ft.)	4
Length (m)	1.2
Flammability Rating	Outer Wall Flame Retardant
Max. Recovered I.D. (In.)	.023
Max. Recovered I.D. (mm)	0.6
Min. Expanded I.D. (In.)	.125
Min. Expanded I.D. (mm)	3.2
Nominal Diameter (In.)	.125
Nominal Diameter (mm)	3.2
Nominal Recovered Wall Thickness (In.)	.038
Nominal Recovered Wall Thickness (mm)	1.0
Pricing Description	Heat Shrink Thin SemRigid, Adhesive .12"(3.2mm) Dia, Black
Shrink Ratio	2.5:1
Temperature Range	-67°F to 230°F (55°C to 110°C)
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.