

Type: Male connector 90° with 4 rows

Termination: Solder

Number of contacts: 64

Pitch: 5.08 mm x 3.81 mm


Operational current: 5.6 A

Packaging: Box

Standard: IEC 60603-2



Technical Specifications on page 36



Accessories

- Coding p. 132

Mating connector / Application:




Type G Female connector (p. 102)



Type G low profile Female connector (p. 104)



Solder - Performance level II

No. of contacts	Pre-mating contact at position	Contact arrangement	Termination length L
			3.0 mm
			Part number
64	without		111-40064
64	Z 2		111-40164
64	Z 2 and Z 32		111-40264

On request

- performance level I + III or customized
- also in THTR
- Board-Lock p. 131
- contact arrangement