




 Slip joint pliers, 8223 - 8226

Slip joint plier with outstanding jaw opening and depth with speedy one hand setting. By pressing the unique thumb operated button the parallel jaws can be adjusted in 9 to 13 positions depending on model.
ISO: 8976
DIN: 8976
Finish: Phosphated, anti-corrosion treated.
Material: Chrome-Vanadium. Specially hardened jaws. Ergonomic handles in two-material combination. Thermoplastic surface for comfortable grip, tough polypropylene core for rigidity.
Shape: With both flat and pipe grip jaws. Specially angled teeth ensure a good grip.
IP = Industrial pack



			A mm	B mm	C mm	D mm	E mm	F mm	
8223	0112685	5	210	35	46	7.0	5	7.0	37 270
8224	0000012	5	250	40	51	8.0	6	8.0	45 350
8225	0000029	5	315	52	63	9.5	7	9.5	55 550
8226	0115853	1	400	60	77	13.0	7	13.0	67 670
8223 IP	0113149	5	210	35	46	7.0	5	7.0	37 270
8224 IP	0101757	5	250	40	51	8.0	6	8.0	45 350
8225 IP	0101764	5	315	52	63	9.5	7	9.5	55 550