






- THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 - MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .054 DIA
 - METAL RETENTION CLIPS ARE INCLUDED IN INSERTS
 - PACKAGE MARKED M 24308/2-299F
 - THIS RCPT. WILL ACCEPT SIZE 22 SOCKET CONTACT M 24308/12 OR AMP # 204351
- AMP PART NO. MARKED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- UL/CSA DESIGNATION MARKED IN THIS AREA,OPTIONAL

OBSOLETE	PHENOLIC, COLOR: BLACK	204528-2
	POLYPHENELYENE SULFIDE (PPS) GST-40F PER MIL-M-24519 OR GLASS FILLED POLYESTER TPES013G30 PER ASTM D5927 COLOR, BLACK	204528-1
	INSERT MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS CHK F.C.BALLEW	12-3-87 1-25-88	TE Connectivity	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD DUM	1-25-88	NAME	AMPLITE RCPT FOR SOCKET CONTACTS HI-DENSITY D CONN, SIZE 3, SERIES 90 WITH FLOAT BUSHINGS
	0 PLC ± -	PRODUCT SPEC		SIZE	CAGE CODE DRAWING NO
	1 PLC ± -	APPLICATION SPEC		RESTRICTED TO	
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT	—	A100779C=204528	—
CUSTOMER DRAWING			SCALE	4:1	SHEET 1 OF 1 REV P