




- Used to fasten and identify bundles at the same time.
- Can be marked with *PANDUIT* Marker Pens.
- Can be custom imprinted with text, symbols or trademarks using *PANDUIT* Custom Hot Stamping Service.
- Can be marked with Computer Printable Labels.

|                               |                                                        |
|-------------------------------|--------------------------------------------------------|
| Part Number:                  | PLF1M-C0                                               |
| Product Family:               | <i>Pan-Ty</i> ® Marker & Flag Ties - Weather Resistant |
| Product Line:                 | Marker Cable Ties                                      |
| RoHS Compliancy Status:       | Compliant                                              |
| Part Description:             | Marker Tie, Flag, 4.3", Miniature cross section        |
| Product Type:                 | Cable Ties                                             |
| Material:                     | Weather Resistant Nylon 6.6                            |
| Color:                        | Black                                                  |
| CSA Certified:                | Yes                                                    |
| UL Listed (File #E56854):     | No                                                     |
| UL Recognized (File #E56854): | Yes                                                    |
| Length (In.):                 | 4.3                                                    |

|                                    |              |
|------------------------------------|--------------|
| Length (mm):                       | 109          |
| Width (In.):                       | .098         |
| Width (mm):                        | 2.5          |
| CE Compliant:                      | Yes          |
| Cross Section:                     | Miniature    |
| Head Height (In.):                 | .154         |
| Head Height (mm):                  | 3.9          |
| Head Width (In.):                  | .180         |
| Head Width (mm):                   | 4.6          |
| Locking Style:                     | Locking      |
| Marker Type:                       | Flag         |
| Marker Write-On Area (In.):        | .31 x .75    |
| Marker Write-On Area (mm):         | 7.9 x 19.1   |
| Material Flammability Rating:      | UL94V-2      |
| Max. Bundle Diameter (In.):        | .87          |
| Max. Bundle Diameter (mm):         | 22           |
| Max. Continuous Use Temperature:   | 185°F (85°C) |
| Min. Loop Tensile Strength (Lbs.): | 18           |
| Min. Loop Tensile Strength (N):    | 80           |

|                  |                                  |
|------------------|----------------------------------|
| Std. Pkg. UOM:   | PK                               |
| Thickness (In.): | .045                             |
| Thickness (mm):  | 1.1                              |
| Tool:            | GTS, GTSL, GS2B, PTS, PPTS, STS2 |
| UOM:             | PC                               |
| Std. Pkg. Qty.:  | 100                              |
| Min. Order Qty.: | 100                              |