




Integrated Device Technology

The Analog and Digital Company™

[Products](#) | [Applications](#) | [Search](#) | [Support](#) | [Investor](#) | [About IDT](#)[9LRS4123A](#)  [9LRS4123AKLF](#)

9LRS4123AKLF

[Description](#) | [Parameters](#) | [Package](#) | [Documents](#) | [Distributor Inventory](#) | [Contacts](#)

DESCRIPTION

PC MAIN CLOCK - PIKETON

Generic Part:

[9LRS4123A](#)

Category:

PARAMETERS

Package	VFQFPN 32
Voltage	1.8V/3V
Temperature	C
Speed	NA

PACKAGE

Package	VFQFPN 32 (NLG32)
Description	VFQFP-N 5 X 5 X 1.0MM NO LEAD
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Pb Free Category	e3 Sn
Mark	K
Package Type	VFQFPN
Lead Count	32
Length	5.0 mm
Width	5.0 mm
Thickness	1.0 mm
Pitch	0.5 mm
Tube / Tray	TRAY
Quantity per Tube/Tray	490
Quantity per Reel	2500
Moisture Sensitivity Level (MSL)	3
Moisture Exposure	168 hrs@<30C/60%
Floor Life	RH
Peak Reflow Temperature	260°C
Rebake Conditions	48hrs@125C
Related Package Documents	view documents

DOCUMENTS

Type	Title	Size	Revision Date
Product Change Notice	PCN# : A1004-01(R1) Alternate Assembly Facilities for VFQFPN-32	131 KB	06/04/2010
	PCN# : A1004-01 Alternate Assembly Facilities for VFQFPN-32	130 KB	04/02/2010
	PCN# : A0910-01 Alternate Assembly Facility for Copper Wire Process on VFQFPN-20, 32, 40, 48, 56	117 KB	11/05/2009

DISTRIBUTOR INVENTORY

Part	Distributor	Qty	Date	RFQ	Order
No matches found.					

CONTACTS

Sales Offices

► [Sales Offices and authorized distributors](#)

Technical Support

Clock Help

► WWW: [Clock Help](#)

Copyright © 2011 Integrated Device Technology, Inc. | [Legal](#) | [Careers](#) | [Contact Us](#) | [myIDT](#) | [Press Room](#) | [Site Map](#)