



## MODULAR JACKS AND PLUGS: GLX Series

### Right Angle Modular Jack

#### Product Features

0.570" Height  
 Snap-In Board Retention Tabs  
 Available in 4, 6, 8 and 10 Position Housings  
 CSA/NRTL Certified File No. LR78160  
 UL File No. E134345

#### Performance Specifications

##### Materials and Finish

##### Housing Material

PBT Thermoplastic, UL 94V-0 Rated

##### Contact Material

Phosphor Bronze

#### Electrical Characteristics

##### Insulation Resistance

500 Megohms Min.

##### Dielectric Withstanding Voltage

1000V RMS, 60Hz

##### Contact Resistance

20 milliohms Max.

##### Current Rating

1.5A

##### Voltage Rating

125V DC



Generated Part Number

GLX-N-66

Part Number Builder

|        |   |               |                      |              |
|--------|---|---------------|----------------------|--------------|
| GLX    | - | N             | 66                   |              |
| Series |   | Shield Option | Positions & Contacts | Other Option |

#### Series

GLX - Right Angle Modular Jack

#### Shield Options

A - Non-Shielded with Panel Stops  
 N - Non-Shielded without Panel Stops

#### Number of Positions / Contacts

44 - 4 Positions / 4 Contacts  
 64 - 6 Positions / 4 Contacts  
 66 - 6 Positions / 6 Contacts

#### Other Option

##### Plating Option

Blank - Gold Flash  
 50 - 50μ" Gold Plating

#### Color Option

Blank - Gray  
 BLK - Black

#### GLX Series

Dimensions in mm

#### GLX-A-44xx

