





REV. 0
DCO 143579

COIL: @ 25°C
RESISTANCE 850 OHMS $\pm$ 10%
NOMINAL VOLTAGE 12.0 VDC
MUST OPERATE 7.8 VDC
MUST RELEASE 4.6 VDC MAX, 1.3 VDC MIN

ENVIRONMENT:
* VIBRATION 10 Hz TO 3000 Hz @ 30 g's
SHOCK 75 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 4.0 MS MAX.
RELEASE 7.5 MS MAX.
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 7 JUN 02

CK 6/7/02

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/21-044L REV.

"JMSDD" RELAY

JMSCDD-12XLS