

datasheet for SEB 2610 F4,8
article number: 972355107



product description:	order number: 972 355-107
description:	Safety built-in socket, 4 mm diameter, contact-protected, with 4.8 x 0.8 tab connector complying with DIN 46 244, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Accessory BES 1000. Installation hole: 12.2 mm diameter. Tightening torque: 50 Ncm.
typ:	SEB 2610 F4,8 weiß/white
system:	4 mm safety system
order number:	972 355-107
color	
other color versions:	
technical data	
measurement category	CAT III
norm	DIN EN 61010-031
type of contact:	unsprung socket
type of termination:	flat plug 4.8 x 0.8
rated voltage:	AC/DC 1000 V
rated current:	25 A
contact resistance:	5 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	gold
housing material:	PA
connecting nut material:	brass nickel-plated
environmental conditions:	
temperature range:	-40 °C to +80 °C
flammable class:	
housing:	94 V-2
drawing	

