


REV.	DATE	DESCRIPTION
A	11/25/03	UPDATE DRAWING FORMAT



8				UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS ARE FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex TNC R/A CRIMP PLUG (FOR RG174/U, 188A/U, 316/U CABLE)
7				UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR MILLIMETERS ARE:	DRAWN	11/25/03	
6				0.5 - 8mm ± 0.20mm	CHECKED		
5	NUT	BRASS	NICKEL	8 - 30mm ± 0.40mm	ISSUED		
4	FERRULE	BRASS	NICKEL	30 - 120mm ± 0.50mm	SHEET	1 OF 1	
3	CONTACT PIN	BRASS	GOLD	UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR INCHES ARE:			PART NO.
2	INSULATOR	DELIRIN	NATURAL	.020 - .315 = ± 0.007"			122148
1	BODY	BRASS	NICKEL	.315 - 1.180 = ± 0.015"			
	DESCRIPTION	MATERIAL	FINISH	1.180 - 4.724 = ± 0.020"	CAD FILE		DWG. NO.
				DO NOT SCALE DRAWING			122148.DWG
							REV. A
							SIZE A
							SCALE NA