


AMP WIRE RANGE	 E13288 Listed
1/0 AWG SOLID OR STRANDED	1/0 AWG STRANDED

 LR7189 Certified	MILITARY P/N AND CLASS
1/0 AWG SOLID OR STRANDED	MS 20659-117 CLASS 2




- 1

TIN PL 0.00254[.000100] MIN THK
PER ASTM B-545
- 2

GOLD PL 0.00127 [.000050] MIN THK
PER MIL-G-45204 OVER NICKEL PL
0.00076 [.000030] MIN THK PER
QQ-C-290

OBSOLETE




COPPER ASTM B-152
1.78 ±0.08 [.070 ±.003]
ANNEALED

~~2-321866-1~~
321866

FINISH

MATERIAL

PART NO.

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 8/30/91		 TE Connectivity						
	DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK RD HEIM 9/30/91	APVD AJ KAUFMAN 9/30/91	NAME TERMINAL, RING TONGUE, SOLISTRAND WIRE SIZE 50.0mm2 [1/0] AWG						
PRODUCT SPEC —											
VOLTAGE RATING: N/A			APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO			
CIRCULAR MIL AREA: 42.4–60.6mm² [83,700–118,500]			MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —	A3	00779	C-321866		—	
CUSTOMER DRAWING				SCALE		2:1		SHEET	1 OF 1	REV	J2