

POSITIONS/ CONTACTS	A		B	
	MM±0.20	[INCH±0.008]	MM±0.30	[INCH±0.012]
02/04	1.00	0.039	2.50	0.098
03/06	2.00	0.079	3.50	0.138
04/08	3.00	0.118	4.50	0.177
05/10	4.00	0.157	5.50	0.217
06/12	5.00	0.197	6.50	0.256
07/14	6.00	0.236	7.50	0.295
08/16	7.00	0.276	8.50	0.335
09/18	8.00	0.315	9.50	0.374
10/20	9.00	0.354	10.50	0.413
11/22	10.00	0.394	11.50	0.453
12/24	11.00	0.433	12.50	0.492
13/26	12.00	0.472	13.50	0.531
14/28	13.00	0.512	14.50	0.571
15/30	14.00	0.551	15.50	0.610
16/32	15.00	0.591	16.50	0.650
17/34	16.00	0.630	17.50	0.689
18/36	17.00	0.669	18.50	0.728
19/38	18.00	0.709	19.50	0.768
20/40	19.00	0.748	20.50	0.807
21/42	20.00	0.787	21.50	0.846
22/44	21.00	0.827	22.50	0.886
23/46	22.00	0.866	23.50	0.925
24/48	23.00	0.906	24.50	0.965
25/50	24.00	0.945	25.50	1.004
26/52	25.00	0.984	26.50	1.043
27/54	26.00	1.024	27.50	1.083
28/56	27.00	1.063	28.50	1.122
29/58	28.00	1.102	29.50	1.161
30/60	29.00	1.142	30.50	1.201
31/62	30.00	1.181	31.50	1.240
32/64	31.00	1.220	32.50	1.280
33/66	32.00	1.260	33.50	1.319
34/68	33.00	1.299	34.50	1.358
35/70	34.00	1.339	35.50	1.398
36/72	35.00	1.378	36.50	1.437
37/74	36.00	1.417	37.50	1.476
38/76	37.00	1.457	38.50	1.516
39/78	38.00	1.496	39.50	1.555
40/80	39.00	1.535	40.50	1.594
41/82	40.00	1.575	41.50	1.634
42/84	41.00	1.614	42.50	1.673
43/86	42.00	1.654	43.50	1.713
44/88	43.00	1.693	44.50	1.752
45/90	44.00	1.732	45.50	1.791
46/92	45.00	1.772	46.50	1.831
47/94	46.00	1.811	47.50	1.870
48/96	47.00	1.850	48.50	1.909
49/98	48.00	1.890	49.50	1.949
50/100	49.00	1.929	50.50	1.988

NOTES:
1. INSULATOR MATERIAL: L.C.P, UL 94V-0, BLACK COLOR.
2. CONTACT MATERIAL: PHOSPHOR BRONZE.
3. CONTACT PLATING: SEE PART NUMBER CODING.
4. CURRENT RATING: 1 AMP.
5. INSULATOR RESISTANCE: 1000 MEGA OHMS MIN.
6. CONTACT RESISTANCE: 20 MILLI OHMS MAX.
7. DIELECTRIC WITHSTANDING: AC 300V.
8. OPERATING TEMPERATURE: -40° C TO +125° C.
9. PROCESSING TEMP.: 260° C FOR 10 SECS MAX.
(INDICATED TEMPERATURE AND TIME IS FOR COMPONENT INSULATOR.
HIGHER PROCESSING TEMPERATURES MAY BE USED, PROVIDED HEAT IS
APPLIED FROM BACK SIDE OF PCB, AND INSULATOR DOES NOT EXCEED
INDICATED TEMPERATURE AND TIME.)

PART NUMBER CODING
SFM210-LP_E-D_-ST-BK

TERMINATION

STRAIGHT




NUMBER OF POSITIONS

(CONTACTS PER ROW, 2 THRU 50)


PLATING

P = GOLD FLASH OVERALL.

S = 10u" GOLD OVERALL,



RECOMMENDED PCB LAYOUT



RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN MM[INCHES]

TOLERANCES:

ANGULAR: ± 5°

.X=± .30 [.012]

.XX=± .20 [.008]

.XXX=± .10 [.004]

SURFACE FINISH: 63 Ra

REMOVE ALL BURRS AND SHARP EDGES .010 MAX

INTERPRET DIMENSIONS AND GEOMETRIC

TOLERANCING PER: ANSI Y14.5M-1994

DRAWN 2/05/09 JH

DATE 2/05/09

NAME JH

THE INFORMATION HEREIN CONTAINS

PROPRIETARY INFORMATION OF

SULLINS ELECTRONICS AND IS NOT

TO BE REPRODUCED, USED OR

DISCLOSED TO OTHERS FOR ANY

PURPOSE EXCEPT AS SPECIFICALLY

AUTHORIZED IN WRITING BY AN

OFFICER OF SULLINS ELECTRONICS.

DESCRIPTION

HEADER, FEMALE 1mm CC, 2 ROWS, ST

SULLINS
CONNECTOR SOLUTIONS

PART NUMBER

SFM210-LP_E-D_-ST-BK

SIZE DWG. NO.

C 11201

REV

A

SCALE: 10:1

SHEET 1 OF 1