


# EDSTL130/X (5.0 mm) EDSTLZ130/X (5.08 mm)



2-24 poles, Spacing 5.0 mm or 5.08 mm

insert required no. of poles **x**

How to order see page 5



## Ratings:

Rated Voltage **300 V**

**250 V**

Rated Current **10 A**

**10 A (T55)**

Rating Impulse Voltage/Dirt Level

**4 kV/3**

## Dimensions

Spacing **5.0 mm (5.08 mm)**

PCB Hole Diameter **1.5 mm**

## Materials

Insulating Material **PA**

Flammability Class **UL94 V-0**

Temperature Range **-30 °C/+105 °C**

Contact Pin **CuZn**

## Color

Black

