







- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS
- 2 SLOT ACCEPTS A 0.54–0.64mm [#23.5–#22] AWG COPPER MAGNET WIRE.
- 3 MATES WITH STANDARD MAG-MATE STYLED POKE-IN TAB TERMINAL.
- 4 WHEN FREE STATE IS COMPRESSED TO 3.23 [.127] DIMENSION GAP BETWEEN SPRING AND CARRIER IS TO BE 0.30 [.012] MAX.
- 5 0.002032 [.000080] MIN TIN OVER 0.00127 [.000050] MIN NICKEL UNDERPLATE.
- 6 PRELIMINARY – NOT FOR PRODUCTION

| LOC |  | DIST |  | REVISIONS |                           |         |       |
|-----|--|------|--|-----------|---------------------------|---------|-------|
| AF  |  | 50   |  | P         | LTR                       | DATE    | OWN   |
|     |  |      |  | A2        | REVISED PER ECR-12-022060 | 26DEC12 | CX LL |

|          |            |             |
|----------|------------|-------------|
| OBSOLETE | —REVERSED— | 1217190-2/6 |
| OBSOLETE | —STANDARD— | 1217190-1   |

REELING PART NUMBER

|                                        |  |  |  |                                                                              |  |  |  |
|----------------------------------------|--|--|--|------------------------------------------------------------------------------|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  |  |  | DWG 19NOV1999                                                                |  |  |  |
|                                        |  |  |  | CHK MICHAEL S. FEHER 22NOV1999                                               |  |  |  |
|                                        |  |  |  | APVD KURT A. RANDOLPH 22NOV1999                                              |  |  |  |
| DIMENSIONS: mm [INCHES]                |  |  |  | NAME Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608 |  |  |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  |  |  | PRODUCT SPEC 108-2012 SPECIAL LEAF CONTACT, 300 SERIES MAG-MATE              |  |  |  |
| 0 PLC ± -                              |  |  |  | APPLICATION SPEC 114-2046                                                    |  |  |  |
| 1 PLC ± -                              |  |  |  | WEIGHT —                                                                     |  |  |  |
| 2 PLC ± 0.25 [.010]                    |  |  |  | SIZE A2                                                                      |  |  |  |
| 3 PLC ± -                              |  |  |  | QAGE CODE 00779                                                              |  |  |  |
| 4 PLC ± -                              |  |  |  | DRAWING NO C=1217190                                                         |  |  |  |
| ANGLES ± -                             |  |  |  | RESTRICTED TO —                                                              |  |  |  |
| MATERIAL 44M BRASS                     |  |  |  | SCALE 10:1                                                                   |  |  |  |
| FINISH 5                               |  |  |  | SHEET 1 of 1                                                                 |  |  |  |
| CUSTOMER DRAWING                       |  |  |  | REV A2                                                                       |  |  |  |