

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0503303033

Status:

Obsolete

Description:

Spade Tongue Terminal for 10 and 12 AWG, Closed Insulated Vinyl Straight Barrel, Yellow, Stud Size 1/4" (M6), Oxygen-Free Copper, Length 32.20mm (1.268")

Documents:

Drawing (PDF)

General

Product Family	Ring and Spade Terminals
Series	50330
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	VSY (Spade Vinyl Straight)
Type	Spade

Physical

Barrel Type	Closed - Brazed
Color - Resin	Yellow
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	1/4" (M6)
Wire Size AWG	10, 12
Wire Size mm²	2.63 - 6.64

Material Info

Reference - Drawing Numbers

Product Specification	PS-50328-002
Sales Drawing	SD-50330-001



Series
image - Reference only

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

50330Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION