



BURNDY Catalog Number
UPC Number
Description
Status

YSM6C
7818108057877
6 AWG PARALLEL SPLICE
Active

Web Use
BURNDY Product Line

Length (in)
Strip Length

Dimensional
0.44
1/2

Product Description

General
Copper Compression Parallel
Splice, 10380-26813 Circular Mil,
0.44" Splice Length, Short Barrel,
Tin Plated

Copper Solid Size (Range)
Copper Stranded (Range)

Conductor(s)
14 AWG-12 AWG
14 AWG-12 AWG

Type of Plating
Plated (Yes or No)

Physical
Tin
Y

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Approvals / Certifications
Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175