


## PRODUCT DATA

### PFA INSULATED CABLES

#### Twin Twisted Pair




- PFA Teflon® insulated twisted pair
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Thermocouple types K & T
- Either solid or stranded conductors available
- Solid 1/0.2mm or 1/0.315mm, or 7/0.2mm stranded
- Available on 50 & 100 metre reels
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- IEC584 colour coded

#### **Codes:**

| Length/Type   | Labfacility code | Stock code | Farnell code |
|---------------|------------------|------------|--------------|
| 50m K 1/0.2   | WK-203 (x50m)    | XF-562-FAR | NEW          |
| 100m K 1/0.2  | WK-203 (x100m)   | XF-563-FAR | NEW          |
| 50m K 1/0.315 | WK-204 (x50m)    | XF-564-FAR | NEW          |
| 50m K 7/0.2   | XS-752 (x50m)    | XF-565-FAR | NEW          |
| 50m T 1/0.2   | WT-304 (x50m)    | XF-558-FAR | NEW          |
| 100m T 1/0.2  | WT-304 (x100m)   | XF-559-FAR | NEW          |
| 50m T 1/0.315 | WT-306 (x50m)    | XF-560-FAR | NEW          |
| 50m T 7/0.2   | WT-307 (x50m)    | XF-561-FAR | NEW          |

## **PFA INSULATED CABLES (continued)**

### **Flat Pair**



- PFA Teflon® insulated flat pair
- Single pair of PFA insulated conductors, laid flat with PFA jacket
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Thermocouple types K, T & N
- Either 1/0.315mm solid (Types K & T), or 7/0.2mm stranded conductors available for types K, T & N
- Available on 25, 50 & 100 metre reels
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- IEC584 colour coded

Codes:

| Length/Type |           | Labfacility code | Stock code | Farnell code |
|-------------|-----------|------------------|------------|--------------|
| 25m         | J 7/0.2   | WJ-248 (x25m)    | XF-566-FAR | NEW          |
| 50m         | J 7/0.2   | WJ-248 (x50m)    | XF-567-FAR | NEW          |
| 25m         | K 1/0.315 | WK-356 (x25m)    | XF-568-FAR | NEW          |
| 25m         | K 7/0.2   | XS-751 (x25m)    | XF-569-FAR | NEW          |
| 50m         | K 7/0.2   | XS-751 (x50m)    | XF-570-FAR | NEW          |
| 100m        | K 7/0.2   | XS-751 (x100m)   | XF-571-FAR | NEW          |
| 25m         | T 1/0.315 | WT-203 (x25m)    | XF-572-FAR | NEW          |
| 25m         | T 7/0.2   | WT-305 (x25m)    | XF-573-FAR | NEW          |
| 50m         | T 7/0.2   | WT-305 (x50m)    | XF-574-FAR | NEW          |
| 100m        | T 7/0.2   | WT-305 (x100m)   | XF-575-FAR | NEW          |
| 25m         | N 7/0.2   | WN-121 (x25m)    | XF-576-FAR | NEW          |