



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	00	M1		REV PER ECO-06-029805	2/6/2007	DW	JL
		M2		REVISED PER ECO-09-020689	02SEP09	KK	AEG



1. USE INSTRUCTION SHEET 9050
⚠ USE HAND TOOL 354940-1
⚠ THIS PART NUMBER IS RESTRICTED, SEE SEPARATE RESTRICTED CUSTOMER DRAWING
⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

RECOMMENDED STRIP LENGTH

	SUPERSEDED	RG-174/U,188/U & 316/U	220210-1	220009-5	30.48 [1.200]	21427-2	9-328666-0	2-221149-0	221455-3	9-228979-1
	SUPERSEDED	RG-59/U,59A/U,59B/U,62/U,62A/U & 62B/U	220189-2	220187-2	30.48 [1.200]	—	9-50428-0	1-221149-3	221455-2	9-228979-0
	OBSOLETE	---	—	—	—	—	—	—	—	1-228979-8
	OBSOLETE	BELDEN YR40862	220189-1	220187-1	30.48 [1.200]	—	9-50427-1	3-221149-6	221455-1	1-228979-7
	SUPERSEDED BY 221199-5	RG-179/U,179A/U,179B/U,187/U & 187A/U	220210-1	220009-5	30.48 [1.200]	21427-2	9-328666-0	3-221149-1	221455-3	1-228979-6
	SUPERSEDED BY 228979-6	—	—	—	—	—	—	—	—	1-228979-5
	SUPERSEDED BY 228979-5	—	—	—	—	—	—	—	—	1-228979-4
	OBSOLETE	BELDEN 9907	220189-1	220187-1	30.48 [1.200]	—	9-50427-1	2-221149-6	221455-5	1-228979-3
	OBSOLETE	BELDEN 8281	—	220189-6	38.10 [1.500]	—	9-331256-0	221149-6	221455-4	228979-8
		RG-174/U,188/U & 316/U	220210-1	220009-5	30.48 [1.200]	21427-2	9-328666-0	2-221149-0	221455-3	228979-7
		RG-59/U,59A/U,59B/U,62/U,62A/U & 62B/U	220189-2	220187-2	30.48 [1.200]	—	9-50428-0	1-221149-3	221455-2	228979-6
		RG-58/U,58A/U,58B/U,58C/U,141/U & 141A/U	220189-1	220187-1	30.48 [1.200]	—	9-50427-1	221149-6	221455-1	228979-5
		FOR USE WITH CABLE	DIE SET		CRIMP TOOL	A				