




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



Customer drawing

REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
1			07/24/08	

D-SUB TECHNICAL DATA

SHELL : Steel, 2.5um (100u") min tin over 1.25um (50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0 Color Black
ELECTRICAL : Voltage rating : 500 V RMS at 50 Hz
Insulation resistance >5000 M Ohms
CLIMATIC : Temperature range -55 °C up to 125°C
MARKING : Amphenol---(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 777RR D 50 P

L: RoHS Compliance

777: tinned shell +
dimples for plug

Shell Size: D

Contact type:
S:Female
P: Male

Configuration: 50

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL	DATE
U.S.	METRIC	DRAWN	Meng.men 07/24/08
.X +/-	0.50	CHECKED	lik.wang 07/24/08
.XX +/-	0.30	CHECKED	
.XXX +/-	0.20		
FRACTIONS +/-			
ANGLES +/-	5°		
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :	
REMOVE SHARP EDGES		ANGLE OF PROJECTION	
DIMENSIONS			
U.S.	INCHES		
METRIC	MM		

Amphenol®

TITLE
stamped and formed connector, RR series

SIZE	DRAWING NO.	REV.
A4	C L777RRD50P	1
SCALE	NONE	SHEET 1 OF 1