



Quartz Crystal


MHz range

SMD-version

model	KX – 5
frequency	32,0 MHz
mode	fundamental
operating temperature	-20° ~ + 70°C
frequency tolerance at +25°C	± 10 ppm
temperature tolerance -20° ~ + 70°C	± 10 ppm
load capacitance C_L	8 pF
series resonance R_1 max.	100 Ohm
aging (first year)	± 2 ppm
shunt capacitance C_0 max.	5,0 pF
drive level max.	50 μ W
RoHS	since production start
contents of reel	1000 pcs.
part no.	12.85526




soldering condition



reel diameter 245 mm

(mm)



suggested soldering pad